

VARISTAR CP PERFORATED DOOR, SEISMIC IP20, MULTI-POINT LOCKING

IP 20 Seismic doors with reinforced and multi-point locking.

The multi-point locking helps achieve necessary contact to avoid EMI effects on electronics.

FEATURES

Perforated door with Multi-Point locking for Seismic & IP 20 applications

Opening angle 180°

Lever handle with push button

SPECIFICATIONS

Table 1/3

Catalog Number	Locking Type	Height	Product Type	Product Family	Works With	Type
21630-876	4-Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-877	4-Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-878	4-Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-879	4-Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-880	4-Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-881	4-Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-882	5-Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-883	5-Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated

Table 2/3

Catalog Number	Rack Height	Width	Complies With	Color	Material	Color Code
21630-876	33 U	600 mm	IEC 61587-1, IEC 61587-2	Black Grey	Steel	RAL 7021

Catalog Number	Rack Height	Width	Complies With	Color	Material	Color Code
21630-877	33 U	800 mm	IEC 61587-1, IEC 61587-2	Black Grey	Steel	RAL 7021
21630-878	38 U	600 mm	IEC 61587-1, IEC 61587-2	Black Grey	Steel	RAL 7021
21630-879	38 U	800 mm	IEC 61587-1, IEC 61587-2	Black Grey	Steel	RAL 7021
21630-880	42 U	600 mm	IEC 61587-1, IEC 61587-2	Black Grey	Steel	RAL 7021
21630-881	42 U	800 mm	IEC 61587-1, IEC 61587-2	Black Grey	Steel	RAL 7021
21630-882	47 U	600 mm	IEC 61587-1, IEC 61587-2	Black Grey	Steel	RAL 7021
21630-883	47 U	800 mm	IEC 61587-1, IEC 61587-2	Black Grey	Steel	RAL 7021

Table 3/3

Catalog Number	Protection Rating
21630-876	IP20
21630-877	IP20
21630-878	IP20
21630-879	IP20
21630-880	IP20
21630-881	IP20
21630-882	IP20
21630-883	IP20

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER