


# SOCKET STRIP, IEC C19



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with IEC C19 outlets.

## CERTIFICATIONS



## FEATURES

Socket strips with C19 IEC sockets

Socket strips can be rotated through all four directions (in 90° increments) during installation

Connecting cable 2 m, with connector in accordance with IEC 60309

Mounting height 1 U

## SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Socket Type	Socket Quantity	Switched Outlets	Color	Voltage AC
60110-280	Socket Strip	IEC C19	8	No	Grey	230V
60110-281	Socket Strip	IEC C19	12	No	Grey	230V
60110-282	Socket Strip	IEC C19	12	No	Grey	230V

Table 2/2

Catalog Number	Height	Length	Depth	Finish	Material	Package Quantity
----------------	--------	--------	-------	--------	----------	------------------

60110-280	44mm	438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-281	44mm	947.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-282	44mm	947.5mm	44mm	Anodized	Aluminum, Polyamide	1

## ADDITIONAL PRODUCT DETAILS

---

Please order bracket for vertical mounting separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
 nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**