



NVENT CADDY MACROFIX PLUS INSULATED



CERTIFICATIONS



FEATURES

Increased opening angle easily accommodates all standard-sized pipes

Quick locking system prevents the hanger from accidentally opening when pipe is moved or adjusted

Quick locking system easily closes with one hand

Return-lip on the hanger prevents the rubber from detaching, eliminating rework during installation

Thread impression retains quick locking captive screw and prevents it from falling out during installation

Combo head bolt works with slotted, hex, or Phillips drivers

Longer ears position the screw farther from the hanger, improving tool clearance when the screw is tightened

Combination nut can be attached to M8 or M10 threaded rod, simplifying material handling

Screw length has been optimized to accommodate an increased pipe range, reducing inventory

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

SPECIFICATIONS

Color: Black

Finish: Electrogalvanized

Material: Steel;EPDM-SBR Rubber

Temperature: -50 to 110 °C

Table 1/2

| Catalog Number | Article Number | Outer Diameter (OD) | Rod Size (RS) | NB/DN | Pipe Size | Width (W) |
|----------------|----------------|---------------------|---------------|-------|-----------|-----------|
| MFP015 | 586701 | 11 - 15 mm | 8, 10 | 8 | 1/4" | 20 mm |
| MFP019 | 586702 | 15 - 19 mm | 8, 10 | 10 | 3/8" | 20 mm |
| MFP025 | 586703 | 19 - 25 mm | 8, 10 | 15 | 1/2" | 20 mm |
| MFP031 | 586704 | 25 - 31 mm | 8, 10 | 20 | 3/4" | 20 mm |
| MFP037 | 586705 | 31 - 37 mm | 8, 10 | 25 | 1" | 20 mm |
| MFP044 | 586706 | 37 - 44 mm | 8, 10 | 32 | 1 1/4" | 20 mm |
| MFP051 | 586707 | 45 - 51 mm | 8, 10 | 40 | 1 1/2" | 21 mm |
| MFP058 | 586708 | 50 - 58 mm | 8, 10 | | | 21 mm |
| MFP068 | 586709 | 58 - 68 mm | 8, 10 | 50 | 2" | 21 mm |
| MFP078 | 586710 | 68 - 78 mm | 8, 10 | 65 | 2 1/2" | 23 mm |
| MFP088 | 586711 | 78 - 88 mm | 8, 10 | | | 23 mm |
| MFP098 | 586712 | 88 - 98 mm | 8, 10 | 80 | 3" | 23 mm |
| MFP108 | 586713 | 98 - 108 mm | 8, 10 | 90 | 3 1/2" | 23 mm |
| MFP118 | 586714 | 108 - 118 mm | 8, 10 | 100 | 4" | 23 mm |
| MFP128 | 586715 | 118 - 128 mm | 8, 10 | | | 23 mm |
| MFP138 | 586716 | 128 - 138 mm | 8, 10 | | | 23 mm |
| MFP148 | 586717 | 138 - 148 mm | 8, 10 | 125 | 5" | 25 mm |
| MFP160 | 586718 | 150 - 160 mm | 8, 10 | | | 25 mm |
| MFP170 | 586719 | 160 - 170 mm | 8, 10 | 150 | 6" | 25 mm |
| MFP200 | 586720 | 190 - 200 mm | 8, 10 | | | 27 mm |
| MFP215 | 586721 | 205 - 215 mm | 8, 10 | | | 27 mm |

Table 2/2

| Catalog Number | Article Number | Thickness (T) | Screw Diameter (Sc) | Screw Length (L) | Static Load (F) |
|----------------|----------------|---------------|---------------------|------------------|-----------------|
| MFP015 | 586701 | 1 mm | 6 | 27mm | 1000N |
| MFP019 | 586702 | 1 mm | 6 | 27mm | 1000N |
| MFP025 | 586703 | 1 mm | 6 | 32mm | 1000N |
| MFP031 | 586704 | 1 mm | 6 | 32mm | 1000N |
| MFP037 | 586705 | 1 mm | 6 | 32mm | 1000N |

| CatalogNumber | Article Number | Thickness (T) | ScrewDiameter (Sc) | Screw Length (L) | Static Load (F) |
|---------------|----------------|---------------|--------------------|------------------|-----------------|
| MFP044 | 586706 | 1 mm | 6 | 37mm | 1000N |
| MFP051 | 586707 | 1.25 mm | 6 | 37mm | 1500N |
| MFP058 | 586708 | 1.25 mm | 6 | 37mm | 1500N |
| MFP068 | 586709 | 1.25 mm | 6 | 40mm | 1500N |
| MFP078 | 586710 | 1.5 mm | 6 | 40mm | 2000N |
| MFP088 | 586711 | 1.5 mm | 6 | 40mm | 2000N |
| MFP098 | 586712 | 1.75 mm | 6 | 45mm | 2500N |
| MFP108 | 586713 | 1.75 mm | 6 | 45mm | 2500N |
| MFP118 | 586714 | 1.75 mm | 6 | 50mm | 2500N |
| MFP128 | 586715 | 2 mm | 6 | 50mm | 3000N |
| MFP138 | 586716 | 2 mm | 6 | 50mm | 3000N |
| MFP148 | 586717 | 2 mm | 6 | 50mm | 3200N |
| MFP160 | 586718 | 2 mm | 6 | 50mm | 3200N |
| MFP170 | 586719 | 2 mm | 6 | 50mm | 3200N |
| MFP200 | 586720 | 2.25 mm | 6 | 50mm | 3600N |
| MFP215 | 586721 | 2.25 mm | 6 | 50mm | 3600N |

ADDITIONAL PRODUCT DETAILS

Lining is EPDM rubber.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER