

VARISTAR CP MOBILE FRAME

Varistar welded steel frame for static load requirements. For 19", ETSI or mounting plate integration. For mobile applications.

FEATURES

Welded, finish powder-coated, black gray, RAL 7021

SPECIFICATIONS

Table 1/3						
Catalog Number	Frame Material	Height	Product Type	Product Family	Works With	Type
20630-193	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-194	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-195	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-196	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-199	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-200	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-201	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-202	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-203	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-204	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-205	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-206	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile

Catalog Number	Frame Material	Height	ProductType	Product Family	Works With	Type
20630-207	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-208	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-209	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-210	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-211	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-212	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-213	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-214	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-215	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-216	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-217	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-218	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-219	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-220	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-221	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-222	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-223	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-224	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-225	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-226	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile

Catalog Number	Frame Material	Height	ProductType	Product Family	Works With	Type
20630-227	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-228	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-229	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-230	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-231	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-232	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-233	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-234	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-235	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-236	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-237	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-238	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-239	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-240	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-241	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-242	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-243	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-244	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-245	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-246	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile

Catalog Number	Frame Material	Height	ProductType	Product Family	Works With	Type
20630-247	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-248	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-249	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-250	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-251	Steel	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-252	Steel	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-253	Steel	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-254	Steel	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-255	Steel	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile
20630-256	Steel	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Mobile

Table 2/3						
Catalog Number	Rack Height	Width	Complies With	Depth	Color	Material
20630-193	24 U	600 mm	IEC 61587-1, IEC 61587-3	600 mm	Black Grey	Steel
20630-194	24 U	600 mm	IEC 61587-1, IEC 61587-3	800 mm	Black Grey	Steel
20630-195	24 U	600 mm	IEC 61587-1, IEC 61587-3	900 mm	Black Grey	Steel
20630-196	24 U	600 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-199	24 U	800 mm	IEC 61587-1, IEC 61587-3	600 mm	Black Grey	Steel
20630-200	24 U	800 mm	IEC 61587-1, IEC 61587-3	800 mm	Black Grey	Steel
20630-201	24 U	800 mm	IEC 61587-1, IEC 61587-3	900 mm	Black Grey	Steel
20630-202	24 U	800 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel

Catalog Number	Rack Height	Width	Complies With	Depth	Color	Material
20630-203	29 U	600 mm	IEC 61587-1, IEC 61587-3	600 mm	Black Grey	Steel
20630-204	29 U	600 mm	IEC 61587-1, IEC 61587-3	800 mm	Black Grey	Steel
20630-205	29 U	600 mm	IEC 61587-1, IEC 61587-3	900 mm	Black Grey	Steel
20630-206	29 U	600 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-207	29 U	800 mm	IEC 61587-1, IEC 61587-3	600 mm	Black Grey	Steel
20630-208	29 U	800 mm	IEC 61587-1, IEC 61587-3	800 mm	Black Grey	Steel
20630-209	29 U	800 mm	IEC 61587-1, IEC 61587-3	900 mm	Black Grey	Steel
20630-210	29 U	800 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-211	33 U	600 mm	IEC 61587-1, IEC 61587-3	600 mm	Black Grey	Steel
20630-212	33 U	600 mm	IEC 61587-1, IEC 61587-3	800 mm	Black Grey	Steel
20630-213	33 U	600 mm	IEC 61587-1, IEC 61587-3	900 mm	Black Grey	Steel
20630-214	33 U	600 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-215	33 U	800 mm	IEC 61587-1, IEC 61587-3	600 mm	Black Grey	Steel
20630-216	33 U	800 mm	IEC 61587-1, IEC 61587-3	800 mm	Black Grey	Steel
20630-217	33 U	800 mm	IEC 61587-1, IEC 61587-3	900 mm	Black Grey	Steel
20630-218	33 U	800 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-219	38 U	600 mm	IEC 61587-1, IEC 61587-3	600 mm	Black Grey	Steel
20630-220	38 U	600 mm	IEC 61587-1, IEC 61587-3	800 mm	Black Grey	Steel
20630-221	38 U	600 mm	IEC 61587-1, IEC 61587-3	900 mm	Black Grey	Steel
20630-222	38 U	600 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel

Catalog Number	Rack Height	Width	Complies With	Depth	Color	Material
20630-223	38 U	800 mm	IEC 61587-1, IEC 61587-3	600 mm	Black Grey	Steel
20630-224	38 U	800 mm	IEC 61587-1, IEC 61587-3	800 mm	Black Grey	Steel
20630-225	38 U	800 mm	IEC 61587-1, IEC 61587-3	900 mm	Black Grey	Steel
20630-226	38 U	800 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-227	42 U	600 mm	IEC 61587-1, IEC 61587-3	600 mm	Black Grey	Steel
20630-228	42 U	600 mm	IEC 61587-1, IEC 61587-3	800 mm	Black Grey	Steel
20630-229	42 U	600 mm	IEC 61587-1, IEC 61587-3	900 mm	Black Grey	Steel
20630-230	42 U	600 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-231	42 U	600 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Steel
20630-232	42 U	600 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Steel
20630-233	42 U	800 mm	IEC 61587-1, IEC 61587-3	600 mm	Black Grey	Steel
20630-234	42 U	800 mm	IEC 61587-1, IEC 61587-3	800 mm	Black Grey	Steel
20630-235	42 U	800 mm	IEC 61587-1, IEC 61587-3	900 mm	Black Grey	Steel
20630-236	42 U	800 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-237	42 U	800 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Steel
20630-238	42 U	800 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Steel
20630-239	47 U	600 mm	IEC 61587-1, IEC 61587-3	600 mm	Black Grey	Steel
20630-240	47 U	600 mm	IEC 61587-1, IEC 61587-3	800 mm	Black Grey	Steel
20630-241	47 U	600 mm	IEC 61587-1, IEC 61587-3	900 mm	Black Grey	Steel
20630-242	47 U	600 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel

Catalog Number	Rack Height	Width	Complies With	Depth	Color	Material
20630-243	47 U	600 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Steel
20630-244	47 U	600 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Steel
20630-245	47 U	800 mm	IEC 61587-1, IEC 61587-3	600 mm	Black Grey	Steel
20630-246	47 U	800 mm	IEC 61587-1, IEC 61587-3	800 mm	Black Grey	Steel
20630-247	47 U	800 mm	IEC 61587-1, IEC 61587-3	900 mm	Black Grey	Steel
20630-248	47 U	800 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-249	47 U	800 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Steel
20630-250	47 U	800 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Steel
20630-251	52 U	600 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-252	52 U	600 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Steel
20630-253	52 U	600 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Steel
20630-254	52 U	800 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-255	52 U	800 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Steel
20630-256	52 U	800 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Steel

Table 3/3		
Catalog Number	Color Code	Static Load
20630-193	RAL 7021	
20630-194	RAL 7021	
20630-195	RAL 7021	
20630-196	RAL 7021	
20630-199	RAL 7021	
20630-200	RAL 7021	
20630-201	RAL 7021	
20630-202	RAL 7021	

Catalog Number	Color Code	Static Load
20630-203	RAL 7021	
20630-204	RAL 7021	
20630-205	RAL 7021	
20630-206	RAL 7021	
20630-207	RAL 7021	
20630-208	RAL 7021	
20630-209	RAL 7021	
20630-210	RAL 7021	
20630-211	RAL 7021	
20630-212	RAL 7021	
20630-213	RAL 7021	
20630-214	RAL 7021	
20630-215	RAL 7021	
20630-216	RAL 7021	
20630-217	RAL 7021	
20630-218	RAL 7021	
20630-219	RAL 7021	
20630-220	RAL 7021	
20630-221	RAL 7021	
20630-222	RAL 7021	
20630-223	RAL 7021	
20630-224	RAL 7021	
20630-225	RAL 7021	
20630-226	RAL 7021	
20630-227	RAL 7021	
20630-228	RAL 7021	
20630-229	RAL 7021	
20630-230	RAL 7021	1600 kgf
20630-231	RAL 7021	1600 kgf
20630-232	RAL 7021	1600 kgf
20630-233	RAL 7021	
20630-234	RAL 7021	
20630-235	RAL 7021	
20630-236	RAL 7021	1600 kgf
20630-237	RAL 7021	1600 kgf

Catalog Number	Color Code	Static Load
20630-238	RAL 7021	1600 kgf
20630-239	RAL 7021	
20630-240	RAL 7021	
20630-241	RAL 7021	
20630-242	RAL 7021	1600 kgf
20630-243	RAL 7021	1600 kgf
20630-244	RAL 7021	1600 kgf
20630-245	RAL 7021	
20630-246	RAL 7021	
20630-247	RAL 7021	
20630-248	RAL 7021	1600 kgf
20630-249	RAL 7021	1600 kgf
20630-250	RAL 7021	1600 kgf
20630-251	RAL 7021	1600 kgf
20630-252	RAL 7021	1600 kgf
20630-253	RAL 7021	1600 kgf
20630-254	RAL 7021	1600 kgf
20630-255	RAL 7021	1600 kgf
20630-256	RAL 7021	1600 kgf

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER