

## PROLINE S1 RACK ANGLES



Rack angles are sold in pairs that are RU marked on all sides. One side is tapped 10-32 while the other side is square hole (.375 x .375 inch). Both sides are spaced per EIA universal standard. Rack angles may be assembled in either tapped or square-hole configuration. Rack angles and mounting brackets are formed from heavy gauge steel. All hardware and brackets are included for assembly into cabinet.

### FEATURES

Rack angles are sold in pairs that are RU marked on all sides

One side is tapped 10-32 while the other side is square hole (.375 x .375 inch)

Both sides are spaced per EIA universal standard

Rack angles may be assembled in either tapped or square-hole configuration

Rack angles and mounting brackets are formed from heavy gauge steel

All hardware and brackets are included for assembly into cabinet

## SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Finish
PS1RA126	36755	1200mm	600mm	600mm	Mild Steel	Powder Coated
PS1RA127	36756	1200mm	700mm	700mm	Mild Steel	Powder Coated
PS1RA217	36758	2100mm	700mm	700mm	Mild Steel	Powder Coated
PS1RA218	36914	2100mm	800mm	800mm	Mild Steel	Powder Coated
PS1RA237	39248	2300mm	700mm	700mm	Mild Steel	Powder Coated
PS1RA238	39251	2300mm	800mm	800mm	Mild Steel	Powder Coated
PS1RA216	36757	2100mm	600mm	600mm	Mild Steel	Powder Coated
PS1RA236	39247	2300mm	600mm	600mm	Mild Steel	Powder Coated

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**