

VARISTAR CP MOBILE BASE/PLINTH

Mobile base/plinth to make a cabinet mobile.

FEATURES

Covers, St, 1.5 mm

Load-carrying capacity on casters 400 kg, on adjustable feet 1000 kg

Support, St, 3 mm

Color RAL 7021

Plinth height H = 103 mm, with feet adjustable from 126 to 134 mm

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Product Family	Works With	Type	Width	Depth
21630-655	Cabinet/Rack Base	Varistar CP	Varistar CP	Base Plinth, Mobile	600 mm	600 mm
21630-656	Cabinet/Rack Base	Varistar CP	Varistar CP	Base Plinth, Mobile	600 mm	800 mm
21630-657	Cabinet/Rack Base	Varistar CP	Varistar CP	Base Plinth, Mobile	600 mm	900 mm
21630-658	Cabinet/Rack Base	Varistar CP	Varistar CP	Base Plinth, Mobile	600 mm	1000 mm
21630-661	Cabinet/Rack Base	Varistar CP	Varistar CP	Base Plinth, Mobile	800 mm	600 mm
21630-662	Cabinet/Rack Base	Varistar CP	Varistar CP	Base Plinth, Mobile	800 mm	800 mm
21630-663	Cabinet/Rack Base	Varistar CP	Varistar CP	Base Plinth, Mobile	800 mm	900 mm
21630-664	Cabinet/Rack Base	Varistar CP	Varistar CP	Base Plinth, Mobile	800 mm	1000 mm

Table 2/2

Catalog Number	Color	Color Code
----------------	-------	------------

21630-655	Black Grey	RAL 7021
21630-656	Black Grey	RAL 7021
21630-657	Black Grey	RAL 7021
21630-658	Black Grey	RAL 7021
21630-661		
21630-662	Black Grey	RAL 7021
21630-663	Black Grey	RAL 7021
21630-664	Black Grey	RAL 7021

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER