



# NVENT CADDY PYRAMID ST ADJUSTABLE STRUT SUPPORT



## FEATURES

- Height adjustability provides effective navigation of pipe, conduit, duct and cable tray around obstructions
- Foam bottom offers low abrasion interface for better roof membrane protection
- Compatible with roof surfaces including single ply, bituminous, metal and spray foam
- Provides superior load distribution, even with varying rooftop surfaces
- Ready to use out of the box, saving installation time and labor
- Multiple sizes and load ratings offer the ability to tailor the solution to the application
- Hot-dip galvanized and UV stabilized for long lasting performance

## SPECIFICATIONS


- Static Load Safety Factor:** 3:1
- Finish:** Hot-Dip Galvanized
- Material:** Polyethylene;Polypropylene;Steel
- Temperature:** -45 to 65 °C

Table 1/2						
Catalog Number	Article Number	Length 1 (L1)	Length 2 (L2)	Height (H)	Width (W)	Surface Area
PSA10CH13	360468	254 mm	317.5 mm	152 - 330 mm	203 mm	59355mm²
PSA16AH18	360469	406 mm	483 mm	178 - 457 mm	203 mm	91613mm²

Table 2/2			
Catalog Number	Article Number	Unit Weight	Static Load (F)

PSA10CH13	360468	2 kg	4450N
PSA16AH18	360469	3 kg	6670N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**  
+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

**Europe**  
Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**  
Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**  
Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500