



# NVENT CADDY ROD LOCK L-BRACKET



## CERTIFICATIONS



## FEATURES

- Easy "push-to-install" design allows installers to simply push the threaded rod through the mounting hole, instantly holding it in position
- Prefabricated assemblies easily lift and lock into place, helping to save time and money
- Multiple attachment holes support the use of either self-drilling screws or bolts, offering installation options for concrete, wood, and steel structures
- Lock nut can be finger tightened, locking the rod in place
- Integrated adjustment nut enables fine tuning the system height up or down
- Extremely useful in tight spaces where wrenches are difficult to use
- Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society ANSI®/MSS-SP-58 (Type 19 and 23)

## SPECIFICATIONS

Table 1/2						
Catalog Number	Material	Finish	Rod Size (RS)	Height (H)	Length (L)	Width (W)
CRLL37EG	Steel	Electrogalvanized	3/8	61.3 mm	43.2 mm	35.6 mm


Table 2/2				
Catalog Number	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Wrench Size	Static Load (F)
CRLL37EG	13 mm	7.1 mm	11/16"	3100N

ADDITIONAL PRODUCT DETAILS

Follow fastener manufacturer’s recommended shear and pull-out strength when fastening to the structure. Fastener not included.

Install in accordance with applicable code.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500