

RAIL WEB MOLD CLAMP, ADJUSTABLE, T20 WELDER STYLE, 57 MM MOLD SIZE, 600 MM MAX JAW OPENING

CATALOG NUMBER

PBC105P1



FEATURES

Adjusts for a wide span of uses including frogs and switches

Lightweight and easy to use

Can also be used on standard (single) rail

SBC105RR provides improved safety with non-sharp profiles and reflecting tape for high visibility

PRODUCT ATTRIBUTES

Welder Style: T20

Mold Size: 57 mm

Jaw Opening: 600mm max

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER