

JOINT BOND MOLD ONLY, POWER, 85-141 LB T-RAIL, 3/0 COMPOSITE, LEFT HAND

CATALOG NUMBER

PBCS6CWPLHM



FEATURES

Replacement mold designed for the installation of jumper bonds to the head of the rail

Connection is made within the confines of the splice plate

PRODUCT ATTRIBUTES

Material: Graphite

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: C

Conductor Size: 3/0 Composite

Conductor Outer Diameter, Nominal: 14.53mm

Orientation: Left Hand

Mold Only: Yes

Welding Material: PB90 or PB90PLUSF80, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER