nVent
DATA-SOLUTIONS

PROLINE S1 CABINET SERVER PKG END, 2150X800X1200, BLACK, STEEL

CATALOG NUMBER

PS1SPE21812B

ProLine S1 Server Package Cabinets are an economical solution for contractors, small computer rooms, schools, retail outlets, or smaller networks that require a general purpose cabinet to house servers, switches, cables and other communication equipment. Multiple sizes, configurations, and accessories give ProLine S1 Cabinets wide application flexibility. ProLine S1 Server Packages are a data center-ready solution designed to be configured in a row or stand-alone configuration. The cabinets feature airflow management and provide easy cable access/mounting provisions.

INDUSTRY STANDARDS

UL 2416 Listed File Number E230874

cUL Listed per CSA 22.2 60950-1-07

UL 2416 Bonding and Grounding (with use of PGK grounding Kit)

EIA 310-D (RU – Rack Unit spacing, marking, and positioning)

IEC 60529, IP20

FEATURES

Top panel has four-corner brush strip cable entry
Internal airflow management
Cable management (750mm and 800mm wide models)
Plinth base
Ability to externally mount cable management (i.e. ladder rack)
Caster/leveler kit pre-installed
PDU mounting brackets included (qty 2 pair)
Joining kits included with “middle” configurations

PRODUCT ATTRIBUTES

Article Number: 39235
Height: 2163mm
Width: 808mm

Depth: 1198mm

Material: Mild Steel

Finish: Powder Coated

Color: Jet Black

Color Code: RAL 9005

Thickness: 1.52mm

Rack Units: 45U

Vertical Cable Manager Accessory: Yes

Sides: Locking panels

Style: End Package

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.