

OPEN FRAME RACK-MOUNT STEEL SHELF



The Open-Frame Rack-Mount Steel Shelf mounts to the front of the rack and is ideal for holding non-19-in. rack-mount equipment. It is available with or without vents. Please note the load rating is 100 lb. (45.4 kg).

FEATURES

The Open-Frame Rack-Mount Steel Shelf mounts to the front of the rack and is ideal for holding non-19-in. rack-mount equipment

It is available with or without vents. Please note the load rating is 100 lb. (45.4 kg)

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Style	Rack Units	Height	Finish	Material
EMS1918	13266	Solid	3U	133mm	Powder Coated	Mild Steel
EMS1922	13267	Solid	3U	133mm	Powder Coated	Mild Steel
EMSV1918	13271	Vented	3U	133mm	Powder Coated	Mild Steel
EMSV1922	13268	Vented	3U	133mm	Powder Coated	Mild Steel

Table 2/2

Catalog Number	Article Number	Color	Color Code	Width	Depth	Thickness
EMS1918	13266	Jet Black	RAL 9005	482mm	457mm	1.52mm
EMS1922	13267	Jet Black	RAL 9005	482mm	559mm	1.52mm
EMSV1918	13271	Jet Black	RAL 9005	482mm	457mm	1.52mm
EMSV1922	13268	Jet Black	RAL 9005	482mm	559mm	1.52mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER