

RACK-MOUNT ADJUSTABLE SHELF



The Rack-Mount Adjustable Shelf mounts to the front surface of front and back rack angles. The adjustable shelf support brackets are clear-plated 12 gauge steel and adjustable to fit multiple-depth enclosures or rack angle placement. There are both solid and vented models available. They fit 19- or 23-inch rack spacing and require only 1U of rack space. Please note the load rating is for 150 lb. (68 kg).

FEATURES

The Rack-Mount Adjustable Shelf mounts to the front surface of front and back rack angles

The adjustable shelf support brackets are clear-plated 12 gauge steel and adjustable to fit multiple-depth enclosures or rack angle placement

There are both solid and vented models available

They fit 19- or 23-inch rack spacing and require only 1U of rack space

Please note the load rating is for 150 lb. (68 kg)

SPECIFICATIONS

Table 1/3

Catalog Number	Article Number	Type	Max Depth	Size	Fits Enclosure Depth Up To	Finish
P19SH68	47399	Solid	780mm	19 in.	800mm	Powder Coated
P19SH68B	47909	Solid	780mm	19 in.	800mm	Powder Coated
P19VSH68B	11053	Vented	780mm	19 in.	800mm	Powder Coated
P19SH810	47409	Solid	980mm	19 in.	1000mm	Powder Coated
P19SH810B	47919	Solid	980mm	19 in.	1000mm	Powder Coated
P19VSH810B	11054	Vented	980mm	19 in.	1000mm	Powder Coated
P23SH68B	12955	Solid	780mm	23 in.	800mm	Powder Coated
P23SH810B	12956	Solid	980mm	23 in.	1000mm	Powder Coated
P23VSH68B	11055	Vented	780mm	23 in.	800mm	Powder Coated

Catalog Number	Article Number	Type	Max Depth	Size	Fits Enclosure Depth Up To	Finish
P23VSH810B	11056	Vented	980mm	23 in.	1000mm	Powder Coated

Table 2/3						
Catalog Number	Article Number	Material	Color	Color Code	Length	Width
P19SH68	47399	Mild Steel	Light Gray	RAL 7035	500mm	439mm
P19SH68B	47909	Mild Steel	Jet Black	RAL 9005	500mm	439mm
P19VSH68B	11053	Mild Steel	Jet Black	RAL 9005	500mm	439mm
P19SH810	47409	Mild Steel	Light Gray	RAL 7035	700mm	439mm
P19SH810B	47919	Mild Steel	Jet Black	RAL 9005	700mm	439mm
P19VSH810B	11054	Mild Steel	Jet Black	RAL 9005	700mm	439mm
P23SH68B	12955	Mild Steel	Jet Black	RAL 9005	500mm	541mm
P23SH810B	12956	Mild Steel	Jet Black	RAL 9005	700mm	541mm
P23VSH68B	11055	Mild Steel	Jet Black	RAL 9005	500mm	541mm
P23VSH810B	11056	Mild Steel	Jet Black	RAL 9005	700mm	541mm

Table 3/3		
Catalog Number	Article Number	Thickness
P19SH68	47399	1.9mm
P19SH68B	47909	1.9mm
P19VSH68B	11053	1.9mm
P19SH810	47409	1.9mm
P19SH810B	47919	1.9mm
P19VSH810B	11054	1.9mm
P23SH68B	12955	1.9mm
P23SH810B	12956	1.9mm
P23VSH68B	11055	1.9mm
P23VSH810B	11056	1.9mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER