

SPECIAL TRACK WORK COMPLETE WELDER, SIGNAL



FEATURES

Molds designed for conductor connections to frog and special track work applications

For use on non-load-bearing rail

Includes mold cleaner and flint ignitor

SPECIFICATIONS

Material: Graphite; Steel

Rail Type: Manganese Frog

Table 1/2

Catalog Number	Bond Terminal Style	Handle Clamp	Conductor Outer Diameter, Nominal	Handle Length	Welder Style	Welding Material
SBTBTB4B	3/4" Tab	B323W, Sold Separately	4.76mm	381mm	TB4	SB25, Sold Separately
SBTBTB4C	1" Tab	B323W, Sold Separately	4.76mm	381mm	TB4	SB25, Sold Separately
SBTBTB4CL	1" Tab	B323P, Sold Separately	4.76mm	584.2mm	TB4	SB25, Sold Separately
SBXSTB4A	1" Tab	B323W, Sold Separately	4.76mm	381mm	TB4	SB25, Sold Separately
SBTBTB4E	1" Tab	B323W, Sold Separately	7.94mm	381mm	TB4	SB32, Sold Separately

Table 2/2

Catalog Number	Conductor Size
SBTBTB4B	3/16" Bondstrand
SBTBTB4C	3/16" Bondstrand
SBTBTB4CL	3/16" Bondstrand
SBXSTB4A	3/16" Bondstrand
SBTBTB4E	5/16" Bondstrand

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER