

VARISTAR CP GLAZED DOOR WITH 1-POINT LOCKING



Varistar CP Glass Door Single Point Locking for IP 20 applications.

FEATURES

St, 1.5 mm

Security glass, 6 mm

Key lock cover

Opening angle 180°

SPECIFICATIONS

Table 1/3

Catalog Number	Type	Locking Type	Protection Rating	Complies With	Product Type	Height
21630-016	Glass Door	Single Point Locking	IP20	IEC 61587-1	Cabinet Door	2000mm
21630-017	Glass Door	Single Point Locking	IP20	IEC 61587-1	Cabinet Door	2200mm
21630-018	Glass Door	Single Point Locking	IP20	IEC 61587-1	Cabinet Door	2000mm
21630-019	Glass Door	Single Point Locking	IP20	IEC 61587-1	Cabinet Door	2200mm

Table 2/3

Catalog Number	Works With	Rack Height	Package Quantity	Finish	Material	Color
21630-016	Varistar CP	42U	1	Powder Coated	Steel, Glass	Black Grey
21630-017	Varistar CP	42U	1	Powder Coated	Steel, Glass	Black Grey

Catalog Number	Works With	Rack Height	Package Quantity	Finish	Material	Color
21630-018	Varistar CP	47U	1	Powder Coated	Steel, Glass	Black Grey
21630-019	Varistar CP	47U	1	Powder Coated	Steel, Glass	Black Grey

Table 3/3

Catalog Number	Color Code	Width
21630-016	RAL 7021	600mm
21630-017	RAL 7021	600mm
21630-018	RAL 7021	800mm
21630-019	RAL 7021	800mm

ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER