

TELECOM MAIN GROUNDING BUSBAR



CERTIFICATIONS



FEATURES

Meets TIA-607-C and TIA-607-D and conforms to BICSI® recommendations

Complies with NEMA® standards

Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)

Telecom grounding busbar splice kits are available to extend the length of the busbar

SPECIFICATIONS

Thickness (T): 6.35 mm
Width (W): 101.6 mm
Material: Copper


Table 1/2

Catalog Number	Tin Plating	Length 1 (L1)	Length 2 (L2)	Hole Size 1 (HS1)	Hole Size 1 Number of Pairs	Hole Size 2 (HS2)
TMGBA12L15P	No	305 mm	229 mm	5/16"	15	7/16"
TMGBA12L15PT	Yes	305 mm	229 mm	5/16"	15	7/16"
TMGBA16L19P	No	394 mm	229 mm	5/16"	19	7/16"
TMGBA16L19PT	Yes	394 mm	229 mm	5/16"	19	7/16"

Catalog Number	Tin Plating	Length 1(L1)	Length 2(L2)	Hole Size 1 (HS1)	Hole Size 1 Number of Pairs	Hole Size 2 (HS2)
TMGBA18L23P	No	451 mm	229 mm	5/16"	23	7/16"
TMGBA18L23PT	Yes	451 mm	229 mm	5/16"	23	7/16"
TMGBA20L27P	No	508 mm	229 mm	5/16"	27	7/16"
TMGBA20L27PT	Yes	508 mm	229 mm	5/16"	27	7/16"
TMGBA24L33P	No	610 mm	457 mm	5/16"	33	7/16"
TMGBA24L33PT	Yes	610 mm	457 mm	5/16"	33	7/16"
TMGBA29L41P	No	737 mm	457 mm	5/16"	41	7/16"
TMGBA29L41PT	Yes	737 mm	457 mm	5/16"	41	7/16"

Table 2/2					
Catalog Number	Hole Size 2 Number of Pairs	A	B	C	D
TMGBA12L15P	3	25.4 mm	28.6 mm	15.9 mm	15.9 mm
TMGBA12L15PT	3	25.4 mm	28.6 mm	15.9 mm	15.9 mm
TMGBA16L19P	3	25.4 mm	28.6 mm	15.9 mm	15.9 mm
TMGBA16L19PT	3	25.4 mm	28.6 mm	15.9 mm	15.9 mm
TMGBA18L23P	3	25.4 mm	28.6 mm	15.9 mm	15.9 mm
TMGBA18L23PT	3	25.4 mm	28.6 mm	15.9 mm	15.9 mm
TMGBA20L27P	3	25.4 mm	28.6 mm	15.9 mm	15.9 mm
TMGBA20L27PT	3	25.4 mm	28.6 mm	15.9 mm	15.9 mm
TMGBA24L33P	5	25.4 mm	28.6 mm	15.9 mm	15.9 mm
TMGBA24L33PT	5	25.4 mm	28.6 mm	15.9 mm	15.9 mm
TMGBA29L41P	5	25.4 mm	28.6 mm	15.9 mm	15.9 mm
TMGBA29L41PT	5	25.4 mm	28.6 mm	15.9 mm	15.9 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction,

property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER