

MAXRACK OPEN FRAME SYSTEM



MaxRack is used for mounting and securing 19- or 23-inch rack equipment that is used in data centers, telecommunication rooms and other locations. These open frame racks are ideal for high-density cabling applications. MaxRack also supports the cabling and cooling needs of large core switches (CISCO Catalyst 6509 / 6513, NEXUS 7010 and NEXUS 7018) by using the combination air baffle/vertical cable manager accessory. MaxRack, with its vast features, supports many diverse applications.

INDUSTRY STANDARDS

UL 1863 Listed; File Number E230874

cUL Listed per CSA C22.2 No. 182.4; File No. E230874

Cisco developer registered

EIA 310-D

FEATURES

Rack can be assembled to accommodate either 19- or 23-inch rack equipment

Racks can be ganged to create rows for high density applications

19-inch configuration equals typical tile width of 24 inch

Flat package to allow easy shipping and handling to job site

Press-in nuts enable single-side easy assembly

All structural members are grounded by special grounding and bonding washers

Top has integrated waterfall, which ensures proper cable radius is achieved

Top and top bracket support accommodate parallel or perpendicular ladder or basket tray mounting applications

Channel uprights provided with hole patterns to support various cable management devices

All RU positions marked with white lettering on front and rear column members

Easy-to-follow complete installation instructions included

Upright channels tapped 12-24 holes per EIA Universal pattern standards

Multiple paint-free grounding points per UL double-lugged standards

SPECIFICATIONS

Material:	Aluminum
Color:	Jet Black
Finish:	Powder Coated
Color Code:	RAL 9005

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Thickness	Rack Units
M8410B45	24288	2188mm	610mm	521mm	3mm	45U
M8416B45	24292	2188mm	610mm	667mm	3mm	45U
M8432B45	24293	2188mm	610mm	1060mm	3mm	45U
M846B45	24287	2188mm	610mm	419mm	3mm	45U
M9610B51	24295	2493mm	610mm	521mm	3mm	51U
M9616B51	24296	2493mm	610mm	667mm	3mm	51U
M9632B51	24297	2493mm	610mm	1060mm	3mm	51U
M966B51	24294	2493mm	610mm	419mm	3mm	51U

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER