

PMC MEZZANINE FRONT PANEL, UNTREATED, WITH EMC SHIELDING



Mezzanine front panel is fitted into PMC front panel cut-outs.
Available in different treatments. For O-ring EMC gasket.

CERTIFICATIONS



FEATURES

Mezzanine front panel is fitted into PMC front panel cut-outs

EMC shielding with conductive O-ring

SPECIFICATIONS

Accessory Type: Front panel

Table 1/3

Catalog Number	Type	Mounting	EMC Shielding	EMC Gasket Type	Material	Front Finish
20835-598	Front Panel without Handle	Screw-on Front	Yes	O-ring	Aluminum	Anodized
20835-889	Front Panel without Handle	Screw-on Front	Yes	O-ring	Aluminum	Anodized
20835-890	Front Panel without Handle	Screw-on Front	Yes		Zinc	
20835-922	Front Panel without Handle	Screw-on Front	Yes		Zinc	Chrome Plated

Catalog Number	Type	Mounting	EMC Shielding	EMC Gasket Type	Material	Front Finish
20835-923	Front Panel without Handle	Screw-on Front	Yes		Zinc	Chrome Plated
20835-893	Front Panel without Handle	Screw-on Front	Yes		Zinc	Chrome Plated
20835-924	Front Panel without Handle	Screw-on Front	Yes		Zinc	Chrome Plated
20835-928	Front Panel without Handle	Screw-on Front	Yes		Zinc	Anodized

Table 2/3						
Catalog Number	Rear Finish	Treated Edges	Height	Width	Depth	Complies With
20835-598	Conductive	No	74mm	12.7mm	2.5mm	PMC Mezzanine, IEEE P1386
20835-889	Conductive	No	74mm	12.7mm	2.5mm	PMC Mezzanine, IEEE P1386
20835-890		No	74mm	12.7mm		PMC Mezzanine, IEEE P1386
20835-922	Chrome Plated	Yes	74mm	12.7mm		PMC Mezzanine, IEEE P1386
20835-923	Chrome Plated	Yes	74mm	12.7mm		PMC Mezzanine, IEEE P1386
20835-893	Chrome Plated	Yes	74mm	12.7mm		PMC Mezzanine, IEEE P1386
20835-924	Chrome Plated	Yes	74mm	12.7mm		PMC Mezzanine, IEEE P1386
20835-928	Conductive	No	74mm	12.7mm		PMC Mezzanine, IEEE P1386

Table 3/3		
Catalog Number	Package Quantity	Finish
20835-598	1	Anodized
20835-889	1	Anodized
20835-890	1	
20835-922	1	
20835-923	1	
20835-893	10	
20835-924	10	
20835-928	10	

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER