

## VARISTAR CP SWING FRAME FOR 800 MM WIDTH

The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° / 160° movement and flexible pivot point.

### FEATURES

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" subracks

120° / 160° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

### SPECIFICATIONS

Table 1/2

| Catalog Number | Height  | Product Type       | Product Family | Rack Height | Width  | Color      |
|----------------|---------|--------------------|----------------|-------------|--------|------------|
| 21630-669      | 1200 mm | Cabinet/Rack Frame | Varistar CP    | 24 U        | 800 mm | Black Grey |
| 21630-680      | 1200 mm | Cabinet/Rack Frame | Varistar CP    | 24 U        | 800 mm | Black Grey |
| 21630-671      | 1400 mm | Cabinet/Rack Frame | Varistar CP    | 29 U        | 800 mm | Black Grey |
| 21630-681      | 1400 mm | Cabinet/Rack Frame | Varistar CP    | 29 U        | 800 mm | Black Grey |
| 21630-673      | 1600 mm | Cabinet/Rack Frame | Varistar CP    | 33 U        | 800 mm | Black Grey |
| 21630-682      | 1600 mm | Cabinet/Rack Frame | Varistar CP    | 33 U        | 800 mm | Black Grey |
| 21630-675      | 1800 mm | Cabinet/Rack Frame | Varistar CP    | 38 U        | 800 mm | Black Grey |
| 21630-683      | 1800 mm | Cabinet/Rack Frame | Varistar CP    | 38 U        | 800 mm | Black Grey |
| 21630-677      | 2000 mm | Cabinet/Rack Frame | Varistar CP    | 42 U        | 800 mm | Black Grey |

| Catalog Number | Height  | ProductType        | Product Family | Rack Height | Width  | Color      |
|----------------|---------|--------------------|----------------|-------------|--------|------------|
| 21630-684      | 2000 mm | Cabinet/Rack Frame | Varistar CP    | 42 U        | 800 mm | Black Grey |
| 21630-679      | 2200 mm | Cabinet/Rack Frame | Varistar CP    | 47 U        | 800 mm | Black Grey |
| 21630-685      | 2200 mm | Cabinet/Rack Frame | Varistar CP    | 47 U        | 800 mm | Black Grey |

| Table 2/2      |          |            |                   |
|----------------|----------|------------|-------------------|
| Catalog Number | Material | Color Code | Protection Rating |
| 21630-669      | Steel    | RAL 7021   | IP20              |
| 21630-680      | Steel    | RAL 7021   | IP20              |
| 21630-671      | Steel    | RAL 7021   | IP20              |
| 21630-681      | Steel    | RAL 7021   | IP20              |
| 21630-673      | Steel    | RAL 7021   | IP20              |
| 21630-682      | Steel    | RAL 7021   | IP20              |
| 21630-675      | Steel    | RAL 7021   | IP20              |
| 21630-683      | Steel    | RAL 7021   | IP20              |
| 21630-677      | Steel    | RAL 7021   | IP20              |
| 21630-684      | Steel    | RAL 7021   | IP20              |
| 21630-679      | Steel    | RAL 7021   | IP20              |
| 21630-685      | Steel    | RAL 7021   | IP20              |

## ADDITIONAL PRODUCT DETAILS

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**