

## C-CHANNEL 2-2 ANGLE BRACKET



### FEATURES

Universally applicable for the construction of assembly systems

### SPECIFICATIONS

**Finish:** Electrogalvanized

**Material:** Steel


Table 1/2

Catalog Number	Article Number	Channel Type	Angle (a)	A	B	C
EBL250A90	584666	E0, E0L, E1	90 °	25 mm	90 mm	4 mm
EBL35A090	587510	E2, E2L, E3, E4	90 °	35 mm	90 mm	4 mm

Table 2/2

Catalog Number	Article Number	D	Hole Size (HS)
EBL250A90	584666	44 mm	10.5 mm
EBL35A090	587510	44 mm	10.5 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**  
+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

**Europe**  
Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**  
Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**  
Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**