

CABLE TO WEB OF RAIL MOLD ONLY, SIGNAL



FEATURES

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

SPECIFICATIONS

Rail Type: 85 lb to 141 lb T-Rail Sections

Material: Graphite

| Table 1/2 | | | | | | |
|----------------|---------------------|------------------------|-----------------------------------|--------------|--------------------------------------|-------------|
| Catalog Number | Bond Terminal Style | Handle Clamp | Conductor Outer Diameter, Nominal | Welder Style | Welding Material | Orientation |
| SBB200CLH | 1" Tab | | 4.76mm | TB5, T21 | SB25, Sold Separately | Left Hand |
| SBB200CRH | 1" Tab | | 4.76mm | TB5, T21 | SB25, Sold Separately | Right Hand |
| SBW3150BLH | 1" Tab | C105B, Sold Separately | 4.76mm | TB5 | SB25 or SB25PLUSF80, Sold Separately | Left Hand |
| SBW3150BRH | 1" Tab | C105B, Sold Separately | 4.76mm | TB5 | SB25 or SB25PLUSF80, Sold Separately | Right Hand |
| SBB200YLH | 1" Tab | C105B, Sold Separately | 5.18mm | T21, TB5 | SB25 or SB25PLUSF80, Sold Separately | Left Hand |

| Catalog Number | Bond Terminal Style | Handle Clamp | Conductor Outer Diameter, Nominal | Welder Style | Welding Material | Orientation |
|----------------|---------------------|------------------------|-----------------------------------|--------------|--------------------------------------|-------------|
| SBB200YRH | 1" Tab | C105B, Sold Separately | 5.18mm | T21, TB5 | SB25 or SB25PLUSF80, Sold Separately | Right Hand |
| SBB200XRH | 1" Tab | | 6.6mm | TB5, T21 | SB32, Sold Separately | Right Hand |
| SBB200PLH | 1" Tab | | 7.75mm | TB5, T21 | SB32, Sold Separately | Left Hand |
| SBB200PRH | 1" Tab | | 7.75mm | TB5, T21 | SB32, Sold Separately | Right Hand |
| SBWW6LH | Field-made | C105B, Sold Separately | 8mm | T21 | SB32 or SB25PLUSF80, Sold Separately | Left Hand |
| SBWW6RH | Field-made | C105B, Sold Separately | 8mm | T21 | SB32 or SB25PLUSF80, Sold Separately | Right Hand |

Table 2/2

| Catalog Number | Conductor Size |
|----------------|-------------------------------|
| SBB200CLH | 3/16" Bondstrand |
| SBB200CRH | 3/16" Bondstrand |
| SBW3150BLH | 3/16" Bondstrand |
| SBW3150BRH | 3/16" Bondstrand |
| SBB200YLH | 16 mm ² Concentric |
| SBB200YRH | 16 mm ² Concentric |
| SBB200XRH | 25 mm ² Stranded |
| SBB200PLH | 35 mm ² Stranded |
| SBB200PRH | 35 mm ² Stranded |
| SBWW6LH | 50 mm ² Solid |
| SBWW6RH | 50 mm ² Solid |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER