

NVENT CADDY CAT HP J-HOOK CLIP TO C PURLIN CLIP, 1.5–6 MM FLANGE

CATALOG NUMBER

CATHPVF14



CERTIFICATIONS



FEATURES

Hammer-on or install from the floor with the VAFT tool

Requires no screws, rivets or special tools for assembly

J-Hooks feature bendable locking tabs that lock on to nVent CADDY Cat HP components to provide rigidity and stability

Link to J-Hooks in one of multiple color options to aid in pathway identification and organization

Customized J-Hook trees can be easily assembled with various J-Hook sizes, colors and configurations

nVent CADDY Cat HP components easily attach to any size nVent CADDY Cat HP J-Hook

PRODUCT ATTRIBUTES

Article Number: 181081


Material: Spring Steel

Finish: nVent CADDY Armour

Flange Thickness (FT): 1.5 – 6mm

Static Load (F): 712N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER