

JOINT BOND MOLD PAIR ONLY, POWER, 85-141 LB T-RAIL, 2/0 ROPELAY

CATALOG NUMBER

**PBC2JM**



FEATURES

- Pair of replacement molds with mounting parts designed for the installation of jumper bonds to the head of the rail
- Connection is made within the confines of the splice plate
- Includes mold cleaner and flint ignitor

PRODUCT ATTRIBUTES

- Material: Graphite
- Rail Type: 85 lb to 141 lb T-Rail Sections
- Bond Terminal Style: C
- Conductor Size: 2/0 Ropelay
- Conductor Outer Diameter, Nominal: 12.19mm
- Mold Only: Yes
- Welding Material: PB65, Sold Separately
- Bond Clip: B194A, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**