

BASIC PDU, EB0403, 400 VAC, 3-PH, 16 A

CATALOG NUMBER

EB0403



Modular, compact PDU. Ultra-Low Profile Design

FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 400 VAC, 3-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

PRODUCT ATTRIBUTES

Product Type: Socket Strip

Socket Type: (36) C13; (6) C19

Socket Quantity: 42

Color: Black

Switched Outlets: No

Circuit Breaker: No Circuit Breaker

Circuit Breaker Quantity: 0

Current Rating: 11A

Finish: Powder Coated

Height: 1490mm

Input Cable Length: 3m

Input Cable Location: Top Feed

Input Current: 16 A

Input Voltage: 380-415 VAC, 3 PH

Max Power Input: 11.0 kVA
Metering Type: None
Nominal Voltage: 415V
On/Off Switch Included: No
Output Voltage: 230VAC
Package Quantity: 1
Plug Type: IEC 60309 516P6 (IP44)
Product Family: Enlogic
Rack Units: 0U
Removable Input Cable: No
Type: Basic PDU

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.