

VARISTAR CP MOBILE FRAME



Varistar welded steel frame for static load requirements. For 19", ETSI or mounting plate integration. For mobile applications.

FEATURES

Welded, finish powder-coated, black gray, RAL 7021

SPECIFICATIONS

Table 1/3

Catalog Number	Type	Frame Material	Static Load	Complies With	Product Type	Height
20630-193	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1200mm
20630-194	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1200mm
20630-195	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1200mm
20630-196	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1200mm
20630-199	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1200mm
20630-200	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1200mm
20630-201	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1200mm
20630-202	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1200mm
20630-203	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1400mm

Catalog Number	Type	Frame Material	Static Load	Complies With	ProductType	Height
20630-204	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1400mm
20630-205	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1400mm
20630-206	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1400mm
20630-207	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1400mm
20630-208	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1400mm
20630-209	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1400mm
20630-210	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1400mm
20630-211	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1600mm
20630-212	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1600mm
20630-213	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1600mm
20630-214	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1600mm
20630-215	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1600mm
20630-216	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1600mm
20630-217	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1600mm
20630-218	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1600mm
20630-219	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1800mm
20630-220	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1800mm
20630-221	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1800mm
20630-222	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1800mm
20630-223	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1800mm

Catalog Number	Type	Frame Material	Static Load	Complies With	ProductType	Height
20630-224	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1800mm
20630-225	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1800mm
20630-226	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	1800mm
20630-227	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-228	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-229	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-230	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-231	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-232	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-233	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-234	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-235	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-236	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-237	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-238	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-239	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-240	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-241	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-242	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-243	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm

Catalog Number	Type	Frame Material	Static Load	Complies With	ProductType	Height
20630-244	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-245	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-246	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-247	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-248	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-249	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-250	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-251	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm
20630-252	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm
20630-253	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm
20630-254	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm
20630-255	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm
20630-256	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm

Table 2/3						
Catalog Number	Works With	Rack Height	Package Quantity	Material	Color	Color Code
20630-193	Varistar CP	24U	1	Steel	Black Grey	RAL 7021
20630-194	Varistar CP	24U	1	Steel	Black Grey	RAL 7021
20630-195	Varistar CP	24U	1	Steel	Black Grey	RAL 7021
20630-196	Varistar CP	24U	1	Steel	Black Grey	RAL 7021
20630-199	Varistar CP	24U	1	Steel	Black Grey	RAL 7021
20630-200	Varistar CP	24U	1	Steel	Black Grey	RAL 7021
20630-201	Varistar CP	24U	1	Steel	Black Grey	RAL 7021
20630-202	Varistar CP	24U	1	Steel	Black Grey	RAL 7021
20630-203	Varistar CP	29U	1	Steel	Black Grey	RAL 7021

Catalog Number	Works With	Rack Height	Package Quantity	Material	Color	Color Code
20630-204	Varistar CP	29U	1	Steel	Black Grey	RAL 7021
20630-205	Varistar CP	29U	1	Steel	Black Grey	RAL 7021
20630-206	Varistar CP	29U	1	Steel	Black Grey	RAL 7021
20630-207	Varistar CP	29U	1	Steel	Black Grey	RAL 7021
20630-208	Varistar CP	29U	1	Steel	Black Grey	RAL 7021
20630-209	Varistar CP	29U	1	Steel	Black Grey	RAL 7021
20630-210	Varistar CP	29U	1	Steel	Black Grey	RAL 7021
20630-211	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-212	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-213	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-214	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-215	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-216	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-217	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-218	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-219	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-220	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-221	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-222	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-223	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-224	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-225	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-226	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-227	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-228	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-229	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-230	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-231	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-232	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-233	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-234	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-235	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-236	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-237	Varistar CP	42U	1	Steel	Black Grey	RAL 7021

Catalog Number	Works With	Rack Height	Package Quantity	Material	Color	Color Code
20630-238	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-239	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-240	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-241	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-242	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-243	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-244	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-245	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-246	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-247	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-248	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-249	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-250	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-251	Varistar CP	52U	1	Steel	Black Grey	RAL 7021
20630-252	Varistar CP	52U	1	Steel	Black Grey	RAL 7021
20630-253	Varistar CP	52U	1	Steel	Black Grey	RAL 7021
20630-254	Varistar CP	52U	1	Steel	Black Grey	RAL 7021
20630-255	Varistar CP	52U	1	Steel	Black Grey	RAL 7021
20630-256	Varistar CP	52U	1	Steel	Black Grey	RAL 7021

Table 3/3		
Catalog Number	Width	Depth
20630-193	600mm	600mm
20630-194	600mm	800mm
20630-195	600mm	900mm
20630-196	600mm	1000mm
20630-199	800mm	600mm
20630-200	800mm	800mm
20630-201	800mm	900mm
20630-202	800mm	1000mm
20630-203	600mm	600mm
20630-204	600mm	800mm
20630-205	600mm	900mm
20630-206	600mm	1000mm
20630-207	800mm	600mm

Catalog Number	Width	Depth
20630-208	800mm	800mm
20630-209	800mm	900mm
20630-210	800mm	1000mm
20630-211	600mm	600mm
20630-212	600mm	800mm
20630-213	600mm	900mm
20630-214	600mm	1000mm
20630-215	800mm	600mm
20630-216	800mm	800mm
20630-217	800mm	900mm
20630-218	800mm	1000mm
20630-219	600mm	600mm
20630-220	600mm	800mm
20630-221	600mm	900mm
20630-222	600mm	1000mm
20630-223	800mm	600mm
20630-224	800mm	800mm
20630-225	800mm	900mm
20630-226	800mm	1000mm
20630-227	600mm	600mm
20630-228	600mm	800mm
20630-229	600mm	900mm
20630-230	600mm	1000mm
20630-231	600mm	1100mm
20630-232	600mm	1200mm
20630-233	800mm	600mm
20630-234	800mm	800mm
20630-235	800mm	900mm
20630-236	800mm	1000mm
20630-237	800mm	1100mm
20630-238	800mm	1200mm
20630-239	600mm	600mm
20630-240	600mm	800mm
20630-241	600mm	900mm
20630-242	600mm	1000mm

Catalog Number	Width	Depth
20630-243	600mm	1100mm
20630-244	600mm	1200mm
20630-245	800mm	600mm
20630-246	800mm	800mm
20630-247	800mm	900mm
20630-248	800mm	1000mm
20630-249	800mm	1100mm
20630-250	800mm	1200mm
20630-251	600mm	1000mm
20630-252	600mm	1100mm
20630-253	600mm	1200mm
20630-254	800mm	1000mm
20630-255	800mm	1100mm
20630-256	800mm	1200mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER