

## 19" FAN UNIT, 1 U, SPEED CONTROL AND MONITORING

Fan Unit for installation into a 1 U space within the Cabinet.



### CERTIFICATIONS



### FEATURES

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

### SPECIFICATIONS

Table 1/1

Catalog Number	Input Voltage DC	Product Type	Input Voltage AC	Accessory Type	Certifications
10713-098	24 V min	Fan Unit		Fan unit, 19"	RoHS, CE, EAC
10713-099	24 V min	Fan Unit		Fan unit, 19"	RoHS, CE, EAC
19713-006		Fan Unit	230 V min	Fan unit, 19"	RoHS, EAC
19713-121		Fan Unit	230 V min	Fan unit, 19"	RoHS, EAC

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**