

BASIC PDU, EB0403, 400 VAC, 3-PH, 16 A

CATALOG NUMBER

EB0403



Modular, compact PDU. Ultra-Low Profile Design

FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 400 VAC, 3-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

PRODUCT ATTRIBUTES

Product Family: Enlogic

Type: Basic PDU

Product Type: Socket Strip

Socket Type: (36) C13; (6) C19

Socket Quantity: 42

Switched Outlets: No

Circuit Breaker: No Circuit Breaker

Circuit Breaker Quantity: 0

Current Rating: 11A

Input Cable Length: 3m

Input Cable Location: Top Feed

Input Current: 16 A

Input Voltage: 380-415 VAC, 3 PH

Max Power Input: 11.0 kVA

Nominal Voltage: 415V
On/Off Switch Included: No
Output Voltage: 230VAC
Plug Type: IEC 60309 516P6 (IP44)
Rack Units: 0U
Removable Input Cable: No
Metering Type: None
Material: Steel
Finish: Powder Coated
Color: Black
Height: 1490mm
Width: 52mm
Depth: 53mm
Weight: 6.11kg
Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.