

# SURGE COUNTER, DIGITAL DISPLAY




## FEATURES

- Records time and date of transient surge events
- Resettable counter
- Snap on, hall effect transducer

## SPECIFICATIONS

| Catalog Number       | DSCL2                   |
|----------------------|-------------------------|
| Trip Threshold       | 100                     |
| Status Indication    | LCD                     |
| Connection, Stranded | 50 mm <sup>2</sup> Max  |
| Lead Length          | 50.8mm                  |
| Enclosure Material   | UL® 94V-0 Thermoplastic |
| Enclosure Rating     | IP 20<br>NEMA®-1        |
| Mounting             | 35 mm top hat DIN rail  |
| Temperature          | -20 to 70 °C            |
| Module Width         | 2 M                     |
| Depth (D)            | 68mm                    |
| Height (H)           | 90 mm                   |
| Width (W)            | 36 mm                   |
| Unit Weight          | 190 kg                  |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**  
+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

**Europe**  
Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**  
Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**  
Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**