

FRONT PANEL, ANODIZED WITH UNTREATED EDGES, UNSHIELDED

Front Panel, anodized with untreated edges, unshielded. The panels enable mounting on horizontal rails.



CERTIFICATIONS



FEATURES

Partial width front panel, Al, 2.5 mm

Al, clear anodized, untreated edges

SPECIFICATIONS

Table 1/3

Catalog Number	Handle Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30818-271	None	No	Anodized	Anodized	No	84 HP
30818-310	None	No	Anodized	Anodized	No	42 HP
30818-331	None	No	Anodized	Anodized	No	63 HP
30818-352	None	No	Anodized	Anodized	No	84 HP
30818-434	None	No	Anodized	Anodized	No	84 HP
30818-556	None	No	Anodized	Anodized	No	42 HP
30818-577	None	No	Anodized	Anodized	No	63 HP
30818-598	None	No	Anodized	Anodized	No	84 HP

Catalog Number	Handle Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30810-433	None	No	Anodized	Anodized	No	2 HP
30818-747	None	Yes	Anodized	Anodized	No	2 HP
30818-272	None	No	Anodized	Anodized	No	3 HP
30818-273	None	No	Anodized	Anodized	No	4 HP
30818-274	None	No	Anodized	Anodized	No	5 HP
30818-275	None	No	Anodized	Anodized	No	6 HP
30818-276	None	No	Anodized	Anodized	No	7 HP
30818-277	None	No	Anodized	Anodized	No	8 HP
30818-279	None	No	Anodized	Anodized	No	10 HP
30818-281	None	No	Anodized	Anodized	No	12 HP
30818-282	None	No	Anodized	Anodized	No	14 HP
30818-284	None	No	Anodized	Anodized	No	16 HP
30818-289	None	No	Anodized	Anodized	No	21 HP
30818-296	None	No	Anodized	Anodized	No	28 HP
30818-517	None	No	Anodized	Anodized	No	3 HP
30818-518	None	No	Anodized	Anodized	No	4 HP
30818-519	None	No	Anodized	Anodized	No	5 HP
30818-520	None	No	Anodized	Anodized	No	6 HP
30818-521	None	No	Anodized	Anodized	No	7 HP
30818-522	None	No	Anodized	Anodized	No	8 HP
30818-524	None	No	Anodized	Anodized	No	10 HP
30818-526	None	No	Anodized	Anodized	No	12 HP
30818-528	None	No	Anodized	Anodized	No	14 HP
30818-530	None	No	Anodized	Anodized	No	16 HP
30818-535	None	No	Anodized	Anodized	No	21 HP
30818-542	None	No	Anodized	Anodized	No	28 HP

Table 2/3

Catalog Number	Package Quantity	Height	Product Type	Type	Rack Height	Width
30818-271	1	84 mm	Front Panel	Front Panel without Handle	2 U	426.4 mm
30818-310	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	213 mm
30818-331	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	319.7 mm

Catalog Number	Package Quantity	Height	ProductType	Type	Rack Height	Width
30818-352	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	426.4 mm
30818-434	1	172.9 mm	Front Panel	Front Panel without Handle	4 U	426.4 mm
30818-556	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	213 mm
30818-577	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	319.7 mm
30818-598	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	426.4 mm
30810-433	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	9.8 mm
30818-747	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	9.8 mm
30818-272	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	14.9 mm
30818-273	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30818-274	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	25 mm
30818-275	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	30.1 mm
30818-276	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	35.2 mm
30818-277	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	40.3 mm
30818-279	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	50.5 mm
30818-281	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	60.6 mm
30818-282	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	70.8 mm
30818-284		128.4 mm	Front Panel	Front Panel without Handle	3 U	80.9 mm
30818-289	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	106.3 mm
30818-296	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	141.9 mm
30818-517		261.8 mm	Front Panel	Front Panel without Handle	6 U	14.9 mm

Catalog Number	Package Quantity	Height	ProductType	Type	Rack Height	Width
30818-518	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	20 mm
30818-519	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	25 mm
30818-520	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	30.1 mm
30818-521	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	35.2 mm
30818-522	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	40.3 mm
30818-524	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	50.5 mm
30818-526	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	60.6 mm
30818-528	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	70.8 mm
30818-530	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	80.9 mm
30818-535	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	106.3 mm
30818-542	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	141.9 mm

Table 3/3

Catalog Number	Complies With	Mounting	Material	Certifications
30818-271	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-310	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-331	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-352	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-434	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-556	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-577	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-598	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS

Catalog Number	Complies With	Mounting	Material	Certifications
30810-433	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-747	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-272	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-273	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-274	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-275	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-276	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-277	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-279	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-281	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-282	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-284	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	
30818-289	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-296	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-517	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	
30818-518	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-519	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-520	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-521	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-522	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-524	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS

Catalog Number	Complies With	Mounting	Material	Certifications
30818-526	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-528	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-530	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-535	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30818-542	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER