



NVENT CADDY PYRAMID H-FRAME KIT



CERTIFICATIONS



FEATURES

- Foam or rubber bottom offers low abrasion interface for better roof membrane protection
- Compatible with roof surfaces including single ply, bituminous, metal and spray foam
- Provides superior load distribution, even with varying rooftop surfaces
- Rubber rooftop interface ideal for solar panel array installations
- Kit includes 2 post bases with pre-installed mounting hardware, 6 bolts, 6 strut nuts, and 2 L-brackets to complete H-frame
- Hot-dip galvanized and UV stabilized for long lasting performance
- Accepts standard strut channels

SPECIFICATIONS

| | |
|----------------------------|----------------------------|
| Static Load Safety Factor: | 3:1 |
| Material: | Polypropylene;Polyethylene |
| Temperature: | -34.4 to 54 °C |

| Table 1/2 | | | | | | |
|----------------|----------------|-------------------|------------|------------|------------|-----------|
| Catalog Number | Article Number | Rooftop Interface | Strut Type | Height (H) | Length (L) | Width (W) |


| | | | | | | |
|------|--------|--------|----------------|--------|--------|--------|
| PHK | 360420 | Foam | A (41 x 41 mm) | 117 mm | 314 mm | 314 mm |
| PHKR | 360421 | Rubber | A (41 x 41 mm) | 118 mm | 314 mm | 314 mm |

| Table 2/2 | | | |
|----------------|----------------|--------------|-----------------|
| Catalog Number | Article Number | Surface Area | Static Load (F) |
| PHK | 360420 | 0.18m² | 6670N |
| PHKR | 360421 | 0.2m² | 6670N |

ADDITIONAL PRODUCT DETAILS

Static load represents 750 lb (3,335 N) per post base. The end user must select and evaluate the strut framing to ensure the assembled H-frame can properly support the applied load.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

| | | | |
|---|--|--|--|
| North America +1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support | Europe Netherlands: +31 800-0200135 France: +33 800 901 793 | Europe Germany: 800 1890272 Other Countries: +31 13 5835404 | APAC Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500 |
|---|--|--|--|