



CE UKCA
EAC
GOST

Material: Body and door are manufactured from 1.2 mm mild steel, front cover and handles manufactured from aluminium.

Rear door: Surface mounted, with 130° opening. Concealed removable hinges, with captive pin. Hinges can be mounted to allow left or right hand opening. Door profiles MMDP are available as an accessory.

Lock: Customised lock, with double grip for easy opening of the door. Double-bit 3 mm insert and 90° movement. Other inserts and locks are available as an accessory.

Protection: IP 55, IK 10.

Finish: RAL 7035 structured powder coating. Top bottom profile RAL7016.

Delivery: Enclosure with aluminium front panel, rear door, plastic double-bit 3 mm key and mounting accessories.

SPECIFICATIONS

Material:	Aluminum; Aluminum
Color:	Light Gray
Finish:	Powder Coated
Color Code:	RAL 7035

Table 1/1					
Catalog Number	Height	Width	Depth	Weight	Quick Ship
OICE303015	300mm	300mm	155mm	4.5kg	No
OICE304021	300mm	400mm	210mm	6.3kg	No
OICE404021	400mm	400mm	210mm	7.3kg	No
OICE406021	400mm	600mm	210mm	9.7kg	No
OICE505021	500mm	500mm	210mm	10.1kg	No
OICE506021	500mm	600mm	210mm	11.3kg	No
OICE606021	600mm	600mm	210mm	11.3kg	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.