



BEAM ATTACHMENT KIT



FEATURES

- For installations where the cable cannot be looped around the steel beam
- Can support two catenary systems using each eye nut as an anchoring point
- Kit includes beam clamps and eye nuts
- Installs on top or bottom flange of I-beams or bar joists

SPECIFICATIONS


Table 1/2						
Catalog Number	Article Number	Material	Finish	Flange Thickness (FT)	Rod Size (RS)	Static Load 1 (F1)
SLBM12	196852	Steel	Electrogalvanized, Hot-Dip Galvanized	10 - 20 mm	12	400N

Table 2/2			
Catalog Number	Article Number	Static Load 2 (F2)	Static Load 3 (F3)
SLBM12	196852	700N	800N

ADDITIONAL PRODUCT DETAILS

Static load 1 represents a point load in the center of the catenary installation. Static load 2 represents a two or three point distributed load on the catenary installation. Static load 3 represents a four or more point distributed load on the catenary installation.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER