

FRONT PANEL, FRONT ANODIZED, REAR CONDUCTIVE, UNSHIELDED

Front panel, unshielded, front anodized and rear conductive.



CERTIFICATIONS



FEATURES

Partial width front panel, Al, 2.5 mm

Al, front anodized, conductive

SPECIFICATIONS

Table 1/3

Catalog Number	Handle Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30838-123	None	No	Anodized	Conductive	No	84 HP
30838-204	None	No	Anodized	Conductive	No	84 HP
30847-465	None	No	Anodized	Conductive	No	84 HP
30847-469	None	No	Anodized	Conductive	No	84 HP
30847-461	None	No	Anodized	Conductive	No	84 HP
30838-081	None	No	Anodized	Conductive	No	42 HP
30838-102	None	No	Anodized	Conductive	No	63 HP
30838-162	None	No	Anodized	Conductive	No	42 HP

Catalog Number	Handle Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30838-183	None	No	Anodized	Conductive	No	63 HP
30847-459	None	No	Anodized	Conductive	No	42 HP
30847-460	None	No	Anodized	Conductive	No	63 HP
30847-463	None	No	Anodized	Conductive	No	42 HP
30847-464	None	No	Anodized	Conductive	No	63 HP
30847-467	None	No	Anodized	Conductive	No	42 HP
30847-468	None	No	Anodized	Conductive	No	63 HP
30847-458	None	No	Anodized	Conductive	No	28 HP
30847-470	None	No	Anodized	Conductive	No	2 HP
30838-067	None	No	Anodized	Conductive	No	28 HP
30838-043	None	No	Anodized	Conductive	No	4 HP
30838-044	None	No	Anodized	Conductive	No	5 HP
30838-045	None	No	Anodized	Conductive	No	6 HP
30838-046	None	No	Anodized	Conductive	No	7 HP
30838-047	None	No	Anodized	Conductive	No	8 HP
30838-049	None	No	Anodized	Conductive	No	10 HP
30838-051	None	No	Anodized	Conductive	No	12 HP
30838-053	None	No	Anodized	Conductive	No	14 HP
30838-055	None	No	Anodized	Conductive	No	16 HP
30838-060	None	No	Anodized	Conductive	No	21 HP
30847-471	None	No	Anodized	Conductive	No	3 HP
30847-476		No	Anodized	Conductive	No	4 HP
30847-462	None	No	Anodized	Conductive	No	28 HP
30838-124	None	No	Anodized	Conductive	No	4 HP
30847-466	None	No	Anodized	Conductive	No	28 HP
30838-125	None	No	Anodized	Conductive	No	5 HP
30838-126	None	No	Anodized	Conductive	No	6 HP
30838-127	None	No	Anodized	Conductive	No	7 HP
30838-128	None	No	Anodized	Conductive	No	8 HP
30838-130	None	No	Anodized	Conductive	No	10 HP
30838-132	None	No	Anodized	Conductive	No	12 HP
30838-134	None	No	Anodized	Conductive	No	14 HP
30838-136	None	No	Anodized	Conductive	No	16 HP
30838-141	None	No	Anodized	Conductive	No	21 HP

Catalog Number	Handle Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30838-148	None	No	Anodized	Conductive	No	28 HP
30847-480		No	Anodized	Conductive	No	8 HP
30847-482		No	Anodized	Conductive	No	10 HP
30847-484		No	Anodized	Conductive	No	12 HP
30847-556	None	No	Anodized	Conductive	No	84 HP

Table 2/3						
Catalog Number	Package Quantity	Height	Product Type	Type	Rack Height	Width
30838-123	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	426.4 mm
30838-204	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	426.4 mm
30847-465	1	172.9 mm	Front Panel	Front Panel without Handle	4 U	426.4 mm
30847-469	1	217.4 mm	Front Panel	Front Panel without Handle	5 U	426.4 mm
30847-461	1	84 mm	Front Panel	Front Panel without Handle	2 U	426.4 mm
30838-081	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	213 mm
30838-102	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	319.7 mm
30838-162	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	213 mm
30838-183	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	319.7 mm
30847-459	1	84 mm	Front Panel	Front Panel without Handle	2 U	213 mm
30847-460	1	84 mm	Front Panel	Front Panel without Handle	2 U	319.7 mm
30847-463	1	172.9 mm	Front Panel	Front Panel without Handle	4 U	213 mm
30847-464	1	172.9 mm	Front Panel	Front Panel without Handle	4 U	319.7 mm
30847-467	1	217.4 mm	Front Panel	Front Panel without Handle	5 U	213 mm
30847-468	1	217.4 mm	Front Panel	Front Panel without Handle	5 U	319.7 mm

Catalog Number	Package Quantity	Height	ProductType	Type	Rack Height	Width
30847-458	5	84 mm	Front Panel	Front Panel without Handle	2 U	141.9 mm
30847-470	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	9.8 mm
30838-067	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	141.9 mm
30838-043	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30838-044	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	25 mm
30838-045	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	30.1 mm
30838-046	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	35.2 mm
30838-047	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	40.3 mm
30838-049	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	50.5 mm
30838-051	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	60.6 mm
30838-053	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	70.8 mm
30838-055		128.4 mm	Front Panel	Front Panel without Handle	3 U	80.9 mm
30838-060	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	106.3 mm
30847-471	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	14.9 mm
30847-476	5	395.1 mm	Front Panel	Front Panel without Handle	4 U	20 mm
30847-462	5	172.9 mm	Front Panel	Front Panel without Handle	4 U	141.9 mm
30838-124	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	20 mm
30847-466	5	217.4 mm	Front Panel	Front Panel without Handle	5 U	141.9 mm
30838-125	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	25 mm
30838-126	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	30.1 mm

Catalog Number	Package Quantity	Height	ProductType	Type	Rack Height	Width
30838-127	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	35.2 mm
30838-128	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	40.3 mm
30838-130	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	50.5 mm
30838-132	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	60.6 mm
30838-134	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	70.8 mm
30838-136	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	80.9 mm
30838-141	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	106.3 mm
30838-148	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	141.9 mm
30847-480	5	395.1 mm	Front Panel	Front Panel without Handle	9 U	40.3 mm
30847-482	5	395.1 mm	Front Panel	Front Panel without Handle	9 U	50.5 mm
30847-484	5	395.1 mm	Front Panel	Front Panel without Handle	9 U	60.6 mm
30847-556	5	395.1 mm	Front Panel	Front Panel without Handle	9 U	426.4 mm

Table 3/3					
Catalog Number	Complies With	Mounting	Material	Certifications	
30838-123	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS	
30838-204	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS	
30847-465	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS	
30847-469	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum		
30847-461	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS	
30838-081	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS	
30838-102	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS	

Catalog Number	Complies With	Mounting	Material	Certifications
30838-162	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-183	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30847-459	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	
30847-460	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	
30847-463	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30847-464	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30847-467	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	
30847-468	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	
30847-458	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	
30847-470	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-067	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-043	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-044	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-045	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-046	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-047	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-049	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-051	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-053	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-055	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-060	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS

Catalog Number	Complies With	Mounting	Material	Certifications
30847-471	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30847-476		Screw-on Front	Aluminum	RoHS
30847-462	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	
30838-124	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30847-466	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	
30838-125	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-126	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-127	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-128	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-130	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-132	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-134	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-136	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-141	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30838-148	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS
30847-480		Screw-on Front	Aluminum	RoHS
30847-482		Screw-on Front	Aluminum	RoHS
30847-484		Screw-on Front	Aluminum	RoHS
30847-556	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER