

C-FIX M T-BOLT



FEATURES

C-Fix quick fit T-bolt

Suitable for C-Profiles 0-4

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/1


Catalog Number	Article Number	Screw Diameter (Sc)	Screw Length (L)	Static Load (F)
CFIXM8030	584530	8	30mm	300N
CFIXM8040	584540	8	40mm	300N
CFIXM8060	584550	8	60mm	300N

ADDITIONAL PRODUCT DETAILS

Sliding force F2 is limited to 600 N for all types of Nuts and T-Bolts for C-channel System.

Nuts and T-Bolts for C-channel System	
C-Channel Type	Pullout Force F1
E0	1100 N
E0L	700 N
E1	1800 N
E2	800 N
E2L	800 N
E3	1500 N
E4	1300 N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
 +1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical Support

Europe
 Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe
 Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC
 Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500