



NVENT CADDY SPEED LINK SLK WITH DECKING HOOK



CERTIFICATIONS



FEATURES

Complete system includes wire, locking device and pre-assembled decking hook end fitting

Quickly and easily attaches to hollow metal decking

Spring-loaded ends snap into decking hole and lock into place

Innovative design helps protect the wire from sharp edges of decking hole, minimizing risk of damage to wire

SPECIFICATIONS

| | |
|-----------------------------------|--------------------------------|
| Static Load Safety Factor: | 5:1 |
| Finish: | Electrogalvanized |
| Material: | Steel;Zinc Alloy;Polypropylene |
| Complies With: | SMACNA HVAC-DCS |

Table 1/2

| Catalog Number | Article Number | Wire Rope Diameter | Wire Rope Length | Roof Decking Sheet Thickness | A | Hole Size (HS) |
|----------------|----------------|--------------------|------------------|------------------------------|--------|----------------|
| SLK15L1DH | 196676 | 1.5 mm | 1m | 1.5 mm Max | 9.2 mm | 8 mm |

| Catalog Number | Article Number | Wire Rope Diameter | Wire Rope Length | RoofDecking Sheet Thickness | A | Hole Size (HS) |
|----------------|----------------|--------------------|------------------|-----------------------------|--------|----------------|
| SLK15L2DH | 196677 | 1.5 mm | 2m | 1.5 mm Max | 9.2 mm | 8 mm |
| SLK2L3DH | 196532 | 2 mm | 3m | 1.5 mm Max | 9.2 mm | 8 mm |
| SLK2L5DH | 196533 | 2 mm | 5m | 1.5 mm Max | 9.2 mm | 8 mm |
| SLK2L7DH | 196534 | 2 mm | 7m | 1.5 mm Max | 9.2 mm | 8 mm |

Table 2/2

| Catalog Number | Article Number | Static Load (F) |
|----------------|----------------|-----------------|
| SLK15L1DH | 196676 | 195N |
| SLK15L2DH | 196677 | 195N |
| SLK2L3DH | 196532 | 440N |
| SLK2L5DH | 196533 | 440N |
| SLK2L7DH | 196534 | 440N |

Thickness (T): 12.5 mm

Width (W): 19 mm

Height (H): 55 mm


Angle (a): 90 ° Max

ADDITIONAL PRODUCT DETAILS

Load rating is only applicable if the load-bearing capacity of the supporting element (steel decking) is adequate.

Check with deck manufacturer for recommended load capacity.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER