

CRIMPING COMPRESSION TOOL DIE, TYPE M2, STANDARD, 120 MM²
STRANDED, 250 KCMIL STRANDED

CATALOG NUMBER

RKM2120



FEATURES

Suitable for cable lugs and connectors

PRODUCT ATTRIBUTES

Article Number: 716938

Lug/Connector Type: Standard

Conductor Size: 120 mm² Stranded; 250 kcmil Stranded

Crimping Width: 5mm

Tool: M2H; M2M

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER