

VARISTAR CP FRAME



Varistar CP welded frame is available for static load requirements and can be integrated with 19", ETSI or mounting plate. Additionally, castors can be added to the frame if needed.

However, if you require castors for your application, you might want to consider a mobile frame that already includes castors.

FEATURES

Welded, finish powder-coated, black gray, RAL 7021

St, 1.5 mm, zinc-plated, with central GND/grounding point

Static load-carrying capacity max. 1600 kg

Please order adjustable feet separately

SPECIFICATIONS

Table 1/3

Catalog Number	Type	Frame Material	Static Load	Complies With	Product Type	Height
20630-065	Standard	Steel			Cabinet/Rack Frame	1200mm
20630-066	Standard	Steel			Cabinet/Rack Frame	1200mm
20630-067	Standard	Steel			Cabinet/Rack Frame	1200mm
20630-068	Standard	Steel			Cabinet/Rack Frame	1200mm
20630-071	Standard	Steel			Cabinet/Rack Frame	1200mm
20630-072	Standard	Steel			Cabinet/Rack Frame	1200mm
20630-073	Standard	Steel			Cabinet/Rack Frame	1200mm

Catalog Number	Type	Frame Material	Static Load	Complies With	ProductType	Height
20630-074	Standard	Steel			Cabinet/Rack Frame	1200mm
20630-075	Standard	Steel			Cabinet/Rack Frame	1400mm
20630-076	Standard	Steel			Cabinet/Rack Frame	1400mm
20630-077	Standard	Steel			Cabinet/Rack Frame	1400mm
20630-078	Standard	Steel			Cabinet/Rack Frame	1400mm
20630-079	Standard	Steel			Cabinet/Rack Frame	1400mm
20630-080	Standard	Steel			Cabinet/Rack Frame	1400mm
20630-081	Standard	Steel			Cabinet/Rack Frame	1400mm
20630-082	Standard	Steel			Cabinet/Rack Frame	1400mm
20630-083	Standard	Steel			Cabinet/Rack Frame	1600mm
20630-084	Standard	Steel			Cabinet/Rack Frame	1600mm
20630-085	Standard	Steel			Cabinet/Rack Frame	1600mm
20630-086	Standard	Steel			Cabinet/Rack Frame	1600mm
20630-087	Standard	Steel			Cabinet/Rack Frame	1600mm
20630-088	Standard	Steel			Cabinet/Rack Frame	1600mm
20630-089	Standard	Steel			Cabinet/Rack Frame	1600mm
20630-090	Standard	Steel			Cabinet/Rack Frame	1600mm
20630-091	Standard	Steel			Cabinet/Rack Frame	1800mm
20630-092	Standard	Steel			Cabinet/Rack Frame	1800mm
20630-093	Standard	Steel			Cabinet/Rack Frame	1800mm

Catalog Number	Type	Frame Material	Static Load	Complies With	ProductType	Height
20630-094	Standard	Steel			Cabinet/Rack Frame	1800mm
20630-095	Standard	Steel			Cabinet/Rack Frame	1800mm
20630-096	Standard	Steel			Cabinet/Rack Frame	1800mm
20630-097	Standard	Steel			Cabinet/Rack Frame	1800mm
20630-098	Standard	Steel			Cabinet/Rack Frame	1800mm
20630-099	Standard	Steel			Cabinet/Rack Frame	2000mm
20630-100	Standard	Steel			Cabinet/Rack Frame	2000mm
20630-101	Standard	Steel			Cabinet/Rack Frame	2000mm
20630-102	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-103	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-104	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-105	Standard	Steel			Cabinet/Rack Frame	2000mm
20630-106	Standard	Steel			Cabinet/Rack Frame	2000mm
20630-107	Standard	Steel			Cabinet/Rack Frame	2000mm
20630-108	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-109	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-110	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm
20630-111	Standard	Steel			Cabinet/Rack Frame	2200mm
20630-112	Standard	Steel			Cabinet/Rack Frame	2200mm
20630-113	Standard	Steel			Cabinet/Rack Frame	2200mm

Catalog Number	Type	Frame Material	Static Load	Complies With	ProductType	Height
20630-114	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-115	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-116	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-117	Standard	Steel			Cabinet/Rack Frame	2200mm
20630-118	Standard	Steel			Cabinet/Rack Frame	2200mm
20630-119	Standard	Steel			Cabinet/Rack Frame	2200mm
20630-120	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-121	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-122	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm
20630-123	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm
20630-124	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm
20630-125	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm
20630-126	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm
20630-127	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm
20630-128	Standard	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm
20630-261	Standard	Steel			Cabinet/Rack Frame	2000mm
20630-262	Standard	Steel			Cabinet/Rack Frame	2200mm

Table 2/3						
Catalog Number	Works With	Rack Height	Package Quantity	Material	Color	Color Code
20630-065	Varistar CP	24U	1	Steel	Black Grey	RAL 7021
20630-066	Varistar CP	24U	1	Steel	Black Grey	RAL 7021
20630-067	Varistar CP	24U	1	Steel	Black Grey	RAL 7021

Catalog Number	Works With	Rack Height	Package Quantity	Material	Color	Color Code
20630-068	Varistar CP	24U	1	Steel	Black Grey	RAL 7021
20630-071	Varistar CP	24U	1	Steel	Black Grey	RAL 7021
20630-072	Varistar CP	24U	1	Steel	Black Grey	RAL 7021
20630-073	Varistar CP	24U	1	Steel	Black Grey	RAL 7021
20630-074	Varistar CP	24U	1	Steel	Black Grey	RAL 7021
20630-075	Varistar CP	29U	1	Steel	Black Grey	RAL 7021
20630-076	Varistar CP	29U	1	Steel	Black Grey	RAL 7021
20630-077	Varistar CP	29U	1	Steel	Black Grey	RAL 7021
20630-078	Varistar CP	29U	1	Steel	Black Grey	RAL 7021
20630-079	Varistar CP	29U	1	Steel	Black Grey	RAL 7021
20630-080	Varistar CP	29U	1	Steel	Black Grey	RAL 7021
20630-081	Varistar CP	29U	1	Steel	Black Grey	RAL 7021
20630-082	Varistar CP	29U	1	Steel	Black Grey	RAL 7021
20630-083	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-084	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-085	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-086	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-087	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-088	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-089	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-090	Varistar CP	33U	1	Steel	Black Grey	RAL 7021
20630-091	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-092	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-093	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-094	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-095	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-096	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-097	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-098	Varistar CP	38U	1	Steel	Black Grey	RAL 7021
20630-099	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-100	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-101	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-102	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-103	Varistar CP	42U	1	Steel	Black Grey	RAL 7021

Catalog Number	Works With	Rack Height	Package Quantity	Material	Color	Color Code
20630-104	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-105	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-106	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-107	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-108	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-109	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-110	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-111	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-112	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-113	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-114	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-115	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-116	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-117	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-118	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-119	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-120	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-121	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-122	Varistar CP	47U	1	Steel	Black Grey	RAL 7021
20630-123	Varistar CP	52U	1	Steel	Black Grey	RAL 7021
20630-124	Varistar CP	52U	1	Steel	Black Grey	RAL 7021
20630-125	Varistar CP	52U	1	Steel	Black Grey	RAL 7021
20630-126	Varistar CP	52U	1	Steel	Black Grey	RAL 7021
20630-127	Varistar CP	52U	1	Steel	Black Grey	RAL 7021
20630-128	Varistar CP	52U	1	Steel	Black Grey	RAL 7021
20630-261	Varistar CP	42U	1	Steel	Black Grey	RAL 7021
20630-262	Varistar CP	47U	1	Steel	Black Grey	RAL 7021

Table 3/3		
Catalog Number	Width	Depth
20630-065	600mm	600mm
20630-066	600mm	800mm
20630-067	600mm	900mm
20630-068	600mm	1000mm
20630-071	800mm	600mm

Catalog Number	Width	Depth
20630-072	800mm	800mm
20630-073	800mm	900mm
20630-074	800mm	1000mm
20630-075	600mm	600mm
20630-076	600mm	800mm
20630-077	600mm	900mm
20630-078	600mm	1000mm
20630-079	800mm	600mm
20630-080	800mm	800mm
20630-081	800mm	900mm
20630-082	800mm	1000mm
20630-083	600mm	600mm
20630-084	600mm	800mm
20630-085	600mm	900mm
20630-086	600mm	1000mm
20630-087	800mm	600mm
20630-088	800mm	800mm
20630-089	800mm	900mm
20630-090	800mm	1000mm
20630-091	600mm	600mm
20630-092	600mm	800mm
20630-093	600mm	900mm
20630-094	600mm	1000mm
20630-095	800mm	600mm
20630-096	800mm	800mm
20630-097	800mm	900mm
20630-098	800mm	1000mm
20630-099	600mm	600mm
20630-100	600mm	800mm
20630-101	600mm	900mm
20630-102	600mm	1000mm
20630-103	600mm	1100mm
20630-104	600mm	1200mm
20630-105	800mm	600mm
20630-106	800mm	800mm

Catalog Number	Width	Depth
20630-107	800mm	900mm
20630-108	800mm	1000mm
20630-109	800mm	1100mm
20630-110	800mm	1200mm
20630-111	600mm	600mm
20630-112	600mm	800mm
20630-113	600mm	900mm
20630-114	600mm	1000mm
20630-115	600mm	1100mm
20630-116	600mm	1200mm
20630-117	800mm	600mm
20630-118	800mm	800mm
20630-119	800mm	900mm
20630-120	800mm	1000mm
20630-121	800mm	1100mm
20630-122	800mm	1200mm
20630-123	600mm	1000mm
20630-124	600mm	1100mm
20630-125	600mm	1200mm
20630-126	800mm	1000mm
20630-127	800mm	1100mm
20630-128	800mm	1200mm
20630-261	600mm	300mm
20630-262	600mm	300mm

ADDITIONAL PRODUCT DETAILS

Castor can be added to the frame. If you will need a castor for your application, you can order a mobile frame which include castors.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER