

CABLE TO WEB OF RAIL MOLD ONLY, POWER, 85-141 LB T-RAIL, 350 KCMIL  
ROPELAY, RIGHT HAND

CATALOG NUMBER

**PBW3FRH**



FEATURES

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

Connections for power or grounding conductor to the neutral axis

PRODUCT ATTRIBUTES

Material: Graphite

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: W

Conductor Size: 350 kcmil Ropelay

Conductor Outer Diameter, Nominal: 22.35mm

Welder Style: T20

Orientation: Right Hand

Mold Only: Yes

Welding Material: PB150 or PB150PLUSF80, Sold Separately

Handle Clamp: C105C, Sold Separately

Conductor Sleeve: S24F, Sold Separately

Hammer Die: WD87, Sold Separately

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**