

PROLINE CONNECTEK COMMUNICATIONS PATCH CABINET



The ProLine Connectek Network Communication/Patch Cabinets feature two vertical cable managers in the front of the cabinet and two rear cable managers for maximum cable routing and support. Cabinets are available in two widths to accommodate high-density cables, patch cords and networking equipment.

FEATURES

Aesthetically pleasing front door offers optimal airflow and durability

Fully perforated top, front door and rear doors allow maximum air movement around cables, patch panels and other network equipment

Front and rear open cable managers provide ability to support and route cable

Side-less models allow for easy installation in ganging applications

Common profiles allow ganging of server and networking cabinets

Top gland plate allows easy routing of cable, pre-terminated cables and patch panels

Three-point locking swing handle allows for easy but controlled access; two keys included

SPECIFICATIONS

Color:	Jet Black
Material:	Mild Steel
Finish:	Powder Coated
Color Code:	RAL 9005

Table 1/2

Catalog Number	Article Number	Sides	Rack Units	Height	Width	Depth
PNC20710B	15614	With sides	42U	1991mm	707mm	999mm
PNC20710BNS	15618	Without sides	42U	1991mm	699mm	999mm
PNC20711B	15615	With sides	42U	1991mm	707mm	1099mm
PNC20711BNS	15621	Without sides	42U	1991mm	699mm	1099mm

Catalog Number	Article Number	Sides	Rack Units	Height	Width	Depth
PNC20712B	15616	With sides	42U	1991mm	707mm	1199mm
PNC20712BNS	15622	Without sides	42U	1991mm	699mm	1199mm
PNC2079B	15613	With sides	42U	1991mm	707mm	899mm
PNC2079BNS	15617	Without sides	42U	1991mm	699mm	899mm
PNC20810B	16066	With sides	42U	1991mm	808mm	999mm
PNC20810BNS	16072	Without sides	42U	1991mm	799mm	999mm
PNC20811B	16067	With sides	42U	1991mm	808mm	1099mm
PNC20811BNS	16073	Without sides	42U	1991mm	799mm	1099mm
PNC20812B	16068	With sides	42U	1991mm	808mm	1199mm
PNC20812BNS	16074	Without sides	42U	1991mm	799mm	1199mm
PNC2089B	16065	With sides	42U	1991mm	808mm	874mm
PNC2089BNS	16071	Without sides	42U	1991mm	799mm	899mm
PNC21810B	26387	With sides	45U	2161mm	806mm	999mm
PNC21811B	26388	With sides	45U	2161mm	806mm	1099mm
PNC21812B	26391	With sides	45U	2161mm	806mm	1199mm
PNC2189B	26386	With sides	45U	2161mm	806mm	899mm
PNC24810B	26393	With sides	51U	2411mm	806mm	999mm
PNC24811B	26394	With sides	51U	2411mm	806mm	1099mm
PNC24812B	26395	With sides	51U	2411mm	806mm	1199mm
PNC2489B	26392	With sides	51U	2411mm	806mm	899mm

Table 2/2		
Catalog Number	Article Number	Thickness
PNC20710B	15614	1.52mm
PNC20710BNS	15618	1.52mm
PNC20711B	15615	1.52mm
PNC20711BNS	15621	1.52mm
PNC20712B	15616	1.52mm
PNC20712BNS	15622	1.52mm
PNC2079B	15613	1.52mm
PNC2079BNS	15617	1.52mm
PNC20810B	16066	1.52mm
PNC20810BNS	16072	1.52mm
PNC20811B	16067	1.52mm
PNC20811BNS	16073	1.52mm

Catalog Number	Article Number	Thickness
PNC20812B	16068	1.52mm
PNC20812BNS	16074	1.52mm
PNC2089B	16065	1.52mm
PNC2089BNS	16071	1.52mm
PNC21810B	26387	1.52mm
PNC21811B	26388	1.52mm
PNC21812B	26391	1.52mm
PNC2189B	26386	1.52mm
PNC24810B	26393	1.52mm
PNC24811B	26394	1.52mm
PNC24812B	26395	1.52mm
PNC2489B	26392	1.52mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER