

MONITOR, KEYBOARD, TOUCHPAD, 1 U DRAWER



Designed for standard 19" rackmount designed for comfort
robust design for heavy use or harsh environment operation

CERTIFICATIONS



FEATURES

Pull-out 17" TFT color monitor chassis, 1 U (resolution 1280 x 1024; connects to VGA interface)

Keyboard with different language keyboard layout (connects via USB)

Integral touchpad (connects via USB)

Voltage supply: Wide-range input (nominal mains voltage 110 to 240 VAC), Voltage supply 12, 24 and 48 VDC on request

Depth-adjustable mounting for different pitches of server panel/slide mounts; Mounting depth (dimension c = spacing of 19" profiles): dimension c 470 ... 740 mm

SPECIFICATIONS

Table 1/2

| Catalog Number | Type | Works With | Color | Color Code | Rack Height | Depth |
|----------------|-----------------------------------|--------------|-----------|------------|-------------|-------|
| 60118-580 | Monitor, Keyboard, Touchpad | 19" Cabinets | Jet Black | RAL 9005 | 1U | 470mm |
| 60118-581 | Monitor, Keyboard, Touchpad | 19" Cabinets | Jet Black | RAL 9005 | 1U | 470mm |

| Catalog Number | Type | Works With | Color | Color Code | Rack Height | Depth |
|----------------|-----------------------------------|--------------|-----------|------------|-------------|-------|
| 60118-582 | Monitor, Keyboard, Touchpad | 19" Cabinets | Jet Black | RAL 9005 | 1U | 470mm |

Table 2/2

| Catalog Number | Package Quantity |
|----------------|------------------|
| 60118-580 | 1 |
| 60118-581 | 1 |
| 60118-582 | 1 |

ADDITIONAL PRODUCT DETAILS

Further versions on request. With trackball or numeric pad.

Other Keyboard layouts see user manual.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER