

## TELESCOPIC SLIDES C-PROFILE FOR CABINET



Telescopic slides with guiding profile for fitting in cabinets with 25 kg load capacity.

### CERTIFICATIONS



### FEATURES

For mounting 84 HP wide sub racks in the 19" plane

Loading capacity: 25 kg per pair

The guiding profile (1) is matched to the fixing dimension in the cabinet (it is bolted to the 19" profile of the cabinet); the adaptor Rail (3) is matched to the depth and fixing dimension on the sub rack (it is inserted into the guiding profile like a telescopic slide)

### SPECIFICATIONS

Table 1/2

Catalog Number	Type	Accessory Type	Product Type	Package Quantity	Finish	Material
24562-473	C Profile	Slide rails	Telescopic Slide	2	Anodized	Aluminum

Table 2/2

Catalog Number	Depth
24562-473	1200mm

## ADDITIONAL PRODUCT DETAILS

---

No protection against extraction, no stop at full extension.

The reinforcement Rail and the C-Rails have been tested in accordance with the Russian atomic energy authority GAN standards.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**