

U-PROFILE FRONT PANEL, SHIELDABLE, D-SUB CUTOUTS



U-profile front panel with cutout for D-Sub connectors.
Shieldable for textile EMC gasket.

CERTIFICATIONS



FEATURES

U-profile, front panel, Aluminum, 2.5 mm, front anodized, rear conductive

For EMC textile gasket

SPECIFICATIONS

| Table 1/3 | | | | | | |
|----------------|-----------------|---------------|--------------|-------------|--------------------|------------|
| Catalog Number | EMC Gasket Type | Treated Edges | Front Finish | Rear Finish | EMC Shielding | Rack Width |
| 30849-749 | Textile | No | Anodized | Conductive | No (Retrofittable) | 4 HP |
| 30849-750 | Textile | No | Anodized | Conductive | No (Retrofittable) | 4 HP |

| Catalog Number | EMC Gasket Type | Treated Edges | Front Finish | Rear Finish | EMC Shielding | Rack Width |
|----------------|-----------------|---------------|--------------|-------------|--------------------|------------|
| 30849-751 | Textile | No | Anodized | Conductive | No (Retrofittable) | 4 HP |
| 30849-752 | Textile | No | Anodized | Conductive | No (Retrofittable) | 4 HP |
| 30849-753 | Textile | No | Anodized | Conductive | No (Retrofittable) | 4 HP |
| 30849-754 | Textile | No | Anodized | Conductive | No (Retrofittable) | 4 HP |
| 30849-755 | Textile | No | Anodized | Conductive | No (Retrofittable) | 4 HP |

| Table 2/3 | | | | | | |
|----------------|------------------|----------|--------------|----------------------------|-------------|-------|
| Catalog Number | Package Quantity | Height | Product Type | Type | Rack Height | Width |
| 30849-749 | 5 | 128.4 mm | Front Panel | Front Panel without Handle | 3 U | 20 mm |
| 30849-750 | 5 | 128.4 mm | Front Panel | Front Panel without Handle | 3 U | 20 mm |
| 30849-751 | 5 | 128.4 mm | Front Panel | Front Panel without Handle | 3 U | 20 mm |
| 30849-752 | 5 | 128.4 mm | Front Panel | Front Panel without Handle | 3 U | 20 mm |
| 30849-753 | 5 | 128.4 mm | Front Panel | Front Panel without Handle | 3 U | 20 mm |
| 30849-754 | 5 | 128.4 mm | Front Panel | Front Panel without Handle | 3 U | 20 mm |
| 30849-755 | 5 | 128.4 mm | Front Panel | Front Panel without Handle | 3 U | 20 mm |

| Table 3/3 | | | |
|----------------|---------------------------------|----------------|----------|
| Catalog Number | Complies With | Mounting | Material |
| 30849-749 | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminum |
| 30849-750 | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminum |
| 30849-751 | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminum |
| 30849-752 | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminum |
| 30849-753 | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminum |

| Catalog Number | Complies With | Mounting | Material |
|----------------|---------------------------------|----------------|----------|
| 30849-754 | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminum |
| 30849-755 | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminum |

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please order textile EMC gasket separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER