

SWAN-NECK LINK, BARE

CATALOG NUMBER

EEBDLC



FEATURES

Standalone link that joins two or more nVent ERICO electrical earth bars

High conductivity, hard drawn, electrolytic tough pitch copper per EN 13601

PRODUCT ATTRIBUTES

Material: Copper

Finish: Bare

Length (L): 125mm

Width (W): 50mm


Thickness (T): 6mm

Unit Weight: 0.3kg

ADDITIONAL PRODUCT DETAILS

Tinned finish is 8 microns according to ASTM B545 Service Class "C" for corrosive environments.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER