

RACK- AND PANEL-MOUNT PDU 6 REC 15A, 19-IN LENGTH, BLACK, STEEL

CATALOG NUMBER

DP1N190615



The Rack- and Panel-Mount PDUs not only provide convenient, reliable power to equipment mounted in cabinets or on open frame racks, but they can also be configured to meet a wide range of design specifications. These PDU's are a basic, lower-cost solution that provide great value.

INDUSTRY STANDARDS

UL/cUL 60950 listed

UL 1449 (Surge protector models only)

EIA 310-D (19-in. rack-mount models only)

FEATURES

Power on/off LED indicates whether power is available at the PDU

External ground stud provided on single-phase models for secure grounding

Circuit breakers provide additional equipment protection

Circuits are isolated on dual circuit model; each has its own circuit breaker

Reset button provides easy access to circuit breaker reset

Surge protector models have an indicator LED to verify surge circuitry protection

Rack-mount models mount directly to rack or with adapter bracket

Rack-mount models designed for single-phase applications

Panel-mount models can be mounted flush or with hanging bracket

Power cord with molded-on plug; 2-in. (305-mm) long single-phase model: 6 ft. (1.8 m); Other single-phase models: 15 ft. (4.6 m)

PRODUCT ATTRIBUTES

Article Number: 16884

Material: Mild Steel

Finish: Textured

Color: Black

Surge Protection: No

Amp Meter Included: No

Electrical Load Rating: 15A
Voltage AC: 120V
Receptacle Location: Front
Receptacle Quantity: 6
Receptacle Style: NEMA 5-15R
Power Cord Plug: NEMA 5-15P
Rack Units: 1U

ADDITIONAL PRODUCT DETAILS

Contact nVent HOFFMAN for custom modifications and non-standard offerings.

Isolate circuits on dual circuit models with separate circuit breakers.

DIAGRAMS

Plugs and Receptacles

Plug Type	Plug	Receptacle
150W 5-15P (100W 5-15P)	5-15P	5-15R
150W 5-15P (100W 5-15P)	5-15P	5-15R
150W 5-15P (100W 5-15P)	5-15P	5-15R
150W 5-15P (100W 5-15P)	5-15P	5-15R
150W 5-15P (100W 5-15P)	5-15P	5-15R

Plug Type	Plug	Receptacle
150W 5-15P (100W 5-15P)	5-15P	5-15R
150W 5-15P (100W 5-15P)	5-15P	5-15R

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.