

SINGLE-SIDED SHELF



The Single-Sided Shelf mounts to 19-inch rack angles to house voice/data networking equipment. Please note the load rating is 75 lb. (34 kg).

FEATURES

The Single-Sided Shelf mounts to 19-inch rack angles to house voice/data networking equipment

Please note the load rating is 75 lb. (34 kg)

SPECIFICATIONS

Color Code: RAL 9005

Table 1/2

Catalog Number	Article Number	Style	Rack Units	Height	Finish	Material
ESH1915	17366	Solid	2U	95mm	Powder Coated	Mild Steel
ESH1915V	17367	Vented	2U	95mm	Powder Coated	Mild Steel
ESH1917	35219	Solid	2U	95mm	Powder Coated	Mild Steel
ESH198	35209	Solid	2U	95mm	Powder Coated	Mild Steel

Table 2/2

Catalog Number	Article Number	Color	Width	Depth	Thickness
ESH1915	17366	Jet Black	482mm	381mm	1.52mm
ESH1915V	17367	Jet Black	482mm	381mm	1.52mm
ESH1917	35219	Jet Black	482mm	432mm	1.52mm
ESH198	35209	Jet Black	482mm	203mm	1.52mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER