

FRONT PANEL, ANODIZED, UNSHIELDED, SCREW ASSEMBLY

Anodized front panel, unshielded version, Al, 2.5 mm.



CERTIFICATIONS



FEATURES

Partial width front panel, Al, 2.5 mm

Al, anodized

SPECIFICATIONS

Table 1/3

Catalog Number	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width	Package Quantity
30807-416	Yes	Anodized	Anodized	No	84 HP	1
30807-494	Yes	Anodized	Anodized	No	42 HP	1
30807-506	Yes	Anodized	Anodized	No	84 HP	1
30807-764	Yes	Anodized	Anodized	No	42 HP	1
30807-771	Yes	Anodized	Anodized	No	63 HP	1
30807-776	Yes	Anodized	Anodized	No	84 HP	1
30808-067	Yes	Anodized	Anodized	No	63 HP	1
30810-432	Yes	Anodized	Anodized	No	2 HP	5

Catalog Number	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width	Package Quantity
30818-741	No	Anodized	Conductive	No	2 HP	5
30807-481	Yes	Anodized	Anodized	No	4 HP	5
30807-482	Yes	Anodized	Anodized	No	6 HP	5
30807-483	Yes	Anodized	Anodized	No	10 HP	5
30807-484	Yes	Anodized	Anodized	No	8 HP	5
30807-485	Yes	Anodized	Anodized	No	12 HP	5
30807-487	Yes	Anodized	Anodized	No	21 HP	5
30807-496	Yes	Anodized	Anodized	No	28 HP	5
30807-501	Yes	Anodized	Anodized	No	14 HP	5
30807-508	Yes	Anodized	Anodized	No	3 HP	5
30807-509	Yes	Anodized	Anodized	No	7 HP	5
30807-510	Yes	Anodized	Anodized	No	5 HP	5
30807-778	Yes	Anodized	Anodized	No	4 HP	5
30807-777	Yes	Anodized	Anodized	No	5 HP	5
30807-752	Yes	Anodized	Anodized	No	6 HP	5
30807-753	Yes	Anodized	Anodized	No	10 HP	5
30807-755	Yes	Anodized	Anodized	No	12 HP	5
30807-757	Yes	Anodized	Anodized	No	21 HP	5
30807-758	Yes	Anodized	Conductive	No	14 HP	5
30807-766	Yes	Anodized	Anodized	No	28 HP	5
30807-779	Yes	Anodized	Anodized	No	8 HP	5
30807-780	Yes	Anodized	Anodized	No	16 HP	5

Table 2/3						
Catalog Number	Height	Product Type	Type	Rack Height	Width	Complies With
30807-416	84 mm	Front Panel	Front Panel without Handle	2 U	426.4 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-494	128.4 mm	Front Panel	Front Panel without Handle	3 U	213 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-506	128.4 mm	Front Panel	Front Panel without Handle	3 U	426.4 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-764	261.8 mm	Front Panel	Front Panel without Handle	6 U	213 mm	IEC 60297-3-101, IEEE 1101.1/10

Catalog Number	Height	ProductType	Type	Rack Height	Width	Complies With
30807-771	261.8 mm	Front Panel	Front Panel without Handle	6 U	319.7 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-776	261.8 mm	Front Panel	Front Panel without Handle	6 U	426.4 mm	IEC 60297-3-101, IEEE 1101.1/10
30808-067	128.4 mm	Front Panel	Front Panel without Handle	3 U	319.7 mm	IEC 60297-3-101, IEEE 1101.1/10
30810-432	128.4 mm	Front Panel	Front Panel without Handle	3 U	9.8 mm	IEC 60297-3-101, IEEE 1101.1/10
30818-741	261.8 mm	Front Panel	Front Panel without Handle	6 U	9.8 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-481	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-482	128.4 mm	Front Panel	Front Panel without Handle	3 U	30.1 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-483	128.4 mm	Front Panel	Front Panel without Handle	3 U	50.5 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-484	128.4 mm	Front Panel	Front Panel without Handle	3 U	40.3 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-485	128.4 mm	Front Panel	Front Panel without Handle	3 U	60.6 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-487	128.4 mm	Front Panel	Front Panel without Handle	3 U	106.3 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-496	128.4 mm	Front Panel	Front Panel without Handle	3 U	141.9 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-501	128.4 mm	Front Panel	Front Panel without Handle	3 U	70.8 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-508	128.4 mm	Front Panel	Front Panel without Handle	3 U	14.9 mm	IEC 60297-3-101, IEEE 1101.1/10

Catalog Number	Height	ProductType	Type	Rack Height	Width	Complies With
30807-509	128.4 mm	Front Panel	Front Panel without Handle	3 U	35.2 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-510	128.4 mm	Front Panel	Front Panel without Handle	3 U	25 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-778	261.8 mm	Front Panel	Front Panel without Handle	6 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-777	261.8 mm	Front Panel	Front Panel without Handle	6 U	25 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-752	261.8 mm	Front Panel	Front Panel without Handle	6 U	30.1 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-753	261.8 mm	Front Panel	Front Panel without Handle	6 U	50.5 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-755	261.8 mm	Front Panel	Front Panel without Handle	6 U	60.6 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-757	261.8 mm	Front Panel	Front Panel without Handle	6 U	106.3 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-758	261.8 mm	Front Panel	Front Panel without Handle	6 U	70.8 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-766	261.8 mm	Front Panel	Front Panel without Handle	6 U	141.9 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-779	261.8 mm	Front Panel	Front Panel without Handle	6 U	40.3 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-780	261.8 mm	Front Panel	Front Panel without Handle	6 U	80.9 mm	IEC 60297-3-101, IEEE 1101.1/10

Table 3/3

Catalog Number	Mounting	Material
30807-416	Screw-on Front	Aluminum
30807-494	Screw-on Front	Aluminum
30807-506	Screw-on Front	Aluminum
30807-764	Screw-on Front	Aluminum

Catalog Number	Mounting	Material
30807-771	Screw-on Front	Aluminum
30807-776	Screw-on Front	Aluminum
30808-067	Screw-on Front	Aluminum
30810-432	Screw-on Front	Aluminum
30818-741	Screw-on Front	Aluminum
30807-481	Screw-on Front	Aluminum
30807-482	Screw-on Front	Aluminum
30807-483	Screw-on Front	Aluminum
30807-484	Screw-on Front	Aluminum
30807-485	Screw-on Front	Aluminum
30807-487	Screw-on Front	Aluminum
30807-496	Screw-on Front	Aluminum
30807-501	Screw-on Front	Aluminum
30807-508	Screw-on Front	Aluminum
30807-509	Screw-on Front	Aluminum
30807-510	Screw-on Front	Aluminum
30807-778	Screw-on Front	Aluminum
30807-777	Screw-on Front	Aluminum
30807-752	Screw-on Front	Aluminum
30807-753	Screw-on Front	Aluminum
30807-755	Screw-on Front	Aluminum
30807-757	Screw-on Front	Aluminum
30807-758	Screw-on Front	Aluminum
30807-766	Screw-on Front	Aluminum
30807-779	Screw-on Front	Aluminum
30807-780	Screw-on Front	Aluminum

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER