

VARISTAR CP GLAZED DOOR WITH 1-POINT LOCKING

FEATURES

St, 1.5 mm

Security glass, 6 mm

Key lock cover

Opening angle 180°

SPECIFICATIONS

Table 1/3

Catalog Number	Locking Type	Height	Product Type	Product Family	Works With	Type
21630-392	Single Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-393	Single Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-481	Single Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-482	Single Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-394	Single Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-395	Single Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-483	Single Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-484	Single Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-396	Single Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-397	Single Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door

Catalog Number	LockingType	Height	ProductType	Product Family	Works With	Type
21630-485	Single Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-486	Single Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-398	Single Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-399	Single Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-487	Single Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-488	Single Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-016	Single Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-017	Single Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-489	Single Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-490	Single Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-018	Single Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-019	Single Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-491	Single Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-492	Single Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door

Table 2/3						
Catalog Number	Rack Height	Width	Complies With	Color	Material	Finish
21630-392	24 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-393	24 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-481	24 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-482	24 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-394	29 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-395	29 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-483	29 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-484	29 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated

Catalog Number	Rack Height	Width	Complies With	Color	Material	Finish
21630-396	33 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-397	33 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-485	33 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-486	33 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-398	38 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-399	38 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-487	38 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-488	38 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-016	42 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-017	42 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-489	42 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-490	42 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-018	47 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-019	47 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-491	47 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-492	47 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated

Table 3/3		
Catalog Number	Color Code	Protection Rating
21630-392	RAL 7021	IP20
21630-393	RAL 7021	IP20
21630-481	RAL 7021	IP20
21630-482	RAL 7021	IP20
21630-394	RAL 7021	IP20
21630-395	RAL 7021	IP20
21630-483	RAL 7021	IP20
21630-484	RAL 7021	IP20
21630-396	RAL 7021	IP20
21630-397	RAL 7021	IP20
21630-485	RAL 7021	IP20
21630-486	RAL 7021	IP20
21630-398	RAL 7021	IP20
21630-399	RAL 7021	IP20
21630-487	RAL 7021	IP20
21630-488	RAL 7021	IP20

Catalog Number	Color Code	Protection Rating
21630-016	RAL 7021	IP20
21630-017	RAL 7021	IP20
21630-489	RAL 7021	IP20
21630-490	RAL 7021	IP20
21630-018	RAL 7021	IP20
21630-019	RAL 7021	IP20
21630-491	RAL 7021	IP20
21630-492	RAL 7021	IP20

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER