

## VARISTAR CP PERFORATED DOOR, SEISMIC IP20, MULTI-POINT LOCKING

IP 20 Seismic doors with reinforced and multi-point locking.

The multi-point locking helps achieve necessary contact to avoid EMI effects on electronics.

### FEATURES

Perforated door with Multi-Point locking for Seismic & IP 20 applications

Opening angle 180°

Lever handle with push button

### SPECIFICATIONS

Table 1/3

| Catalog Number | Locking Type    | Height  | Product Type | Product Family | Works With  | Type                   |
|----------------|-----------------|---------|--------------|----------------|-------------|------------------------|
| 21630-876      | 4-Point Locking | 1600 mm | Cabinet Door | Varistar CP    | Varistar CP | Steel Door, Perforated |
| 21630-877      | 4-Point Locking | 1600 mm | Cabinet Door | Varistar CP    | Varistar CP | Steel Door, Perforated |
| 21630-878      | 4-Point Locking | 1800 mm | Cabinet Door | Varistar CP    | Varistar CP | Steel Door, Perforated |
| 21630-879      | 4-Point Locking | 1800 mm | Cabinet Door | Varistar CP    | Varistar CP | Steel Door, Perforated |
| 21630-880      | 4-Point Locking | 2000 mm | Cabinet Door | Varistar CP    | Varistar CP | Steel Door, Perforated |
| 21630-881      | 4-Point Locking | 2000 mm | Cabinet Door | Varistar CP    | Varistar CP | Steel Door, Perforated |
| 21630-882      | 5-Point Locking | 2200 mm | Cabinet Door | Varistar CP    | Varistar CP | Steel Door, Perforated |
| 21630-883      | 5-Point Locking | 2200 mm | Cabinet Door | Varistar CP    | Varistar CP | Steel Door, Perforated |

Table 2/3

| Catalog Number | Rack Height | Width  | Complies With            | Color      | Material | Color Code |
|----------------|-------------|--------|--------------------------|------------|----------|------------|
| 21630-876      | 33 U        | 600 mm | IEC 61587-1, IEC 61587-2 | Black Grey | Steel    | RAL 7021   |

| Catalog Number | Rack Height | Width  | Complies With            | Color      | Material | Color Code |
|----------------|-------------|--------|--------------------------|------------|----------|------------|
| 21630-877      | 33 U        | 800 mm | IEC 61587-1, IEC 61587-2 | Black Grey | Steel    | RAL 7021   |
| 21630-878      | 38 U        | 600 mm | IEC 61587-1, IEC 61587-2 | Black Grey | Steel    | RAL 7021   |
| 21630-879      | 38 U        | 800 mm | IEC 61587-1, IEC 61587-2 | Black Grey | Steel    | RAL 7021   |
| 21630-880      | 42 U        | 600 mm | IEC 61587-1, IEC 61587-2 | Black Grey | Steel    | RAL 7021   |
| 21630-881      | 42 U        | 800 mm | IEC 61587-1, IEC 61587-2 | Black Grey | Steel    | RAL 7021   |
| 21630-882      | 47 U        | 600 mm | IEC 61587-1, IEC 61587-2 | Black Grey | Steel    | RAL 7021   |
| 21630-883      | 47 U        | 800 mm | IEC 61587-1, IEC 61587-2 | Black Grey | Steel    | RAL 7021   |

Table 3/3

| Catalog Number | Protection Rating |
|----------------|-------------------|
| 21630-876      | IP20              |
| 21630-877      | IP20              |
| 21630-878      | IP20              |
| 21630-879      | IP20              |
| 21630-880      | IP20              |
| 21630-881      | IP20              |
| 21630-882      | IP20              |
| 21630-883      | IP20              |

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**