


PLUG-IN UNIT KIT WITH IET HANDLE, SHIELDED, BLACK 3 U



Plug-in unit, with IET inserter/extractor black handle, 3 U, front assembly. The U-shaped front panel enable shielding with a textile gasket.

CERTIFICATIONS



FEATURES

U-shaped front panel for textile gasket

Suitable for insertion and extraction forces up to 700 N (per pair)

Enable the installation of a microswitch

Enable the installation of coding pegs in accordance with IEC 60297-3-103/ IEEE 1101.10

SPECIFICATIONS

Table 1/3

Catalog Number	Type	Handle Type	Mounting	EMC Shielding	EMC Gasket Type	Material
20848-763	Front Panel with Handle (PIU)	IET	Screw-on Front	Yes	Textile	Aluminum
20848-764	Front Panel with Handle (PIU)	IET	Screw-on Front	Yes	Textile	Aluminum
20848-765	Front Panel with Handle (PIU)	IET	Screw-on Front	Yes	Textile	Aluminum

Table 2/3

Catalog Number	Front Finish	Rear Finish	Treated Edges	Rack Height	Height	Rack Width
20848-763	Anodized	Etched	No	3U	128.4mm	4HP
20848-764	Anodized	Etched	No	3U	128.4mm	8HP
20848-765	Anodized	Etched	No	3U	128.4mm	12HP

Table 3/3

Catalog Number	Width	Complies With	Package Quantity	Finish
20848-763	20mm	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	1	Anodized, Passivated
20848-764	40.3mm	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	1	Anodized, Passivated
20848-765	60.6mm	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	1	Anodized, Passivated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER