

PLUG-IN UNIT KIT WITH TRAPEZOID HANDLE, SHIELDED, GREY



Plug-in unit, with static handle and U-shaped front panel. The grey handle is assembled on the front panel. The U-shaped panel enables the assembly of a textile gasket.

CERTIFICATIONS



FEATURES

Front panel, U-profile, shielded

Handle without extraction function

SPECIFICATIONS

Table 1/3

Catalog Number	Type	Handle Type	Mounting	EMC Shielding	EMC Gasket Type	Material
20848-663	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum
20848-664	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum
20848-665	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum
20848-666	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum
20848-667	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum

Catalog Number	Type	Handle Type	Mounting	EMC Shielding	EMC Gasket Type	Material
20848-668	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum
20848-669	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum
20848-670	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum
20848-671	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum
20848-672	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum
20848-673	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum
20848-674	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum
20848-675	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum
20848-676	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum
20848-677	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum
20848-678	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	Yes	Textile	Aluminum


Table 2/3						
Catalog Number	Front Finish	Rear Finish	Treated Edges	Rack Height	Height (H)	Rack Width
20848-663	Anodized	Etched	No	3U	128.4mm	3HP
20848-664	Anodized	Etched	No	3U	128.4mm	4HP
20848-665	Anodized	Etched	No	3U	128.4mm	5HP
20848-666	Anodized	Etched	No	3U	128.4mm	6HP
20848-667	Anodized	Etched	No	3U	128.4mm	7HP
20848-668	Anodized	Etched	No	3U	128.4mm	8HP
20848-669	Anodized	Etched	No	3U	128.4mm	10HP
20848-670	Anodized	Etched	No	3U	128.4mm	12HP
20848-671	Anodized	Etched	No	6U	261.8mm	3HP
20848-672	Anodized	Etched	No	6U	261.8mm	4HP
20848-673	Anodized	Etched	No	6U	261.8mm	5HP
20848-674	Anodized	Etched	No	6U	261.8mm	6HP
20848-675	Anodized	Etched	No	6U	261.8mm	7HP

Catalog Number	Front Finish	Rear Finish	Treated Edges	Rack Height	Height (H)	Rack Width
20848-676	Anodized	Etched	No	6U	261.8mm	8HP
20848-677	Anodized	Etched	No	6U	261.8mm	10HP
20848-678	Anodized	Etched	No	6U	261.8mm	12HP

Table 3/3					
Catalog Number	Width (W)	Complies With	Flammability Rating	Package Quantity	Finish
20848-663	14.9mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20848-664	20mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20848-665	25mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20848-666	30.1mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20848-667	35.2mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20848-668	40.3mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20848-669	50.5mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20848-670	60.6mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20848-671	14.9mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20848-672	20mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20848-673	25mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20848-674	30.1mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated

CatalogNumber	Width (W)	Complies With	Flammability Rating	Package Quantity	Finish
20848-675	35.2mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20848-676	40.3mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20848-677	50.5mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20848-678	60.6mm	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER